


●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。



面付ラッチ錠 LOCKS WITH LATCHES

A-1378-P | A-378-P
ステンレス製 鋼製

特徴 Feature

- ・ステンレス製で耐食性に優れています。(A-1378-P)
- ・面付けタイプで取付けが簡単です。
- ・掘込みタイプに比べメンテナンスが非常に簡単です。
- ・建築錠前各社の錠前の組込みが可能です。
- ・右開き用・左開き用(本図写真共右開き用です。)
- ・Corrosion-resistant stainless steel is used. (A-1378-P)
- ・Surface attachment type: it's easy to install.
- ・Maintenance is very simple when compared with the embedded type.
- ・Locks by construction lock makers can be incorporated.
- ・The left-hand or right-hand use. (Drawings and photo show the right-hand use)

[A-1378-P]

仕様・材質

本体・表面パネル／ステンレス鋼板(SUS304)
ハンドル・サムターン・キャップ／
ステンレス鋼鋳物(SCS13)

- ・表面仕上: ヘアーライン仕上

[A-378-P]

仕様・材質

本体・表面パネル／冷間圧延鋼板(SPCC)
表面パネルカバー／ステンレス鋼板(SUS304)
ハンドル・サムターン・キャップ／亜鉛合金(ZDC)
ライナー／ステンレス鋼板(SUS304)

- ・表面仕上
 - 本体・表面パネル／亜鉛めっきクロメート処理(MFZn-C)
 - 表面パネルカバー／ヘアーライン仕上
 - ハンドル・サムターン・キャップ／焼付塗装(シリバーメタリック)

- ・適用厚扉: 35~45mm
- ・鍵番号: 37500G
- ・付属品: キー2本・取付け用ビス・ライナー
- ・シェルター・キャビン・格納庫
- ・特注品...納期ご連絡致します

用
途
期

[A-1378-P]

- Specifications
- Material: Main body/Front panel: Stainless steel plate (SUS304). Handle/Thumb turn/Cap: Cast stainless steel (SCS13)
 - Finish: Hairline finish

[A-378-P]

- Specifications
- Material: Main body/Front panel: Cold rolled steel plate (SPCC). Front panel cover: Stainless steel plate (SUS304). Handle/Thumb turn/Cap: Zinc alloy (ZDC). Liner: Stainless steel plate (SUS304)
 - Finish: Main body/Front panel: Zinc plating chromate treatment (MFZn-C). Front panel cover: Hairline finish
 - Handle/Thumb turn/Cap: Baked (Silver metallic)
 - Applicable door thickness: 35 to 45mm
 - Key No.: 37500G
 - Accessories: Two keys, installation screws and liner

Specific use

• Shelters, cabins and storage houses



[A-1378-P]



- Specifications
- Material: Main body/Front panel: Stainless steel plate (SUS304). Handle/Thumb turn/Cap: Cast stainless steel (SCS13)
 - Finish: Hairline finish

[A-378-P]

- Specifications
- Material: Main body/Front panel: Cold rolled steel plate (SPCC). Front panel cover: Stainless steel plate (SUS304). Handle/Thumb turn/Cap: Zinc alloy (ZDC). Liner: Stainless steel plate (SUS304)
 - Finish: Main body/Front panel: Zinc plating chromate treatment (MFZn-C). Front panel cover: Hairline finish
 - Handle/Thumb turn/Cap: Baked (Silver metallic)
 - Applicable door thickness: 35 to 45mm
 - Key No.: 37500G
 - Accessories: Two keys, installation screws and liner

Specific use

• Shelters, cabins and storage houses



商品番号 Product No.	RoHS CAD	備考 Remarks	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price
			2,230		Quantity	単価 Price
A-1378-P-L		左開き用 Left-hand use		03066	¥29,000	5個～ ¥27,840
A-1378-P-R	2D	右開き用 Right-hand use		03067	¥29,000	5個～ ¥27,840
A-378-P-L		左開き用 Left-hand use		03064	¥15,000	5個～ ¥14,400
A-378-P-R		右開き用 Right-hand use		03065	¥15,000	5個～ ¥14,400