

Ball End L-Wrenches

- ProGuard™ Finish -

L-Wrenches

- Ball End inserts into a screw at a 25° angle
- Ball End saves time by quickly funneling tool into screw
- 25° angle allows natural hand and wrist movement
- Superior Ball End strength and working angle
- Works in hard to reach places



Sets	PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY	LIST
Inch	10945	BLX7	7	Long	5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	1	
	10932	BLX8	8	Long	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	1	
	10938	BLX10	10	Long	1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	1	
	10936	BLX12	12	Long	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16"	1	
	10937	BLX13	13	Long	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1	
	10935	BLX15	15	Long	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2" (in vinyl roll up pouch)	1	
	10933	MBLX13	13	Long	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8" (in metal box)	1	
	16037	BLX13XL	13	Extra Long	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1	

SINGLE PACKAGING														
PACKAGED BULK TAGGED/BARCODED														
Singles	SIZE	INCH	MM	INCH	MM	PART#	QTY	LIST EA	PART#	QTY	LIST EA	PART#	QTY	LIST EA
LONG Inch	.050	2.8	72	0.53	13	10902	10		12902	100		15702	10	
	1/16	3.0	76	0.56	14	10903	10		12903	100		15703	10	
	5/64	3.2	81	0.61	15	10904	10		12904	100		15704	10	
	3/32	3.4	86	0.65	16	10905	10		12905	100		15705	10	
	7/64	3.6	90	0.70	18	10906	10		12906	100		15706	10	
	1/8	3.8	95	0.75	19	10907	10		12907	100		15707	10	
	9/64	4.0	101	0.80	20	10908	10		12908	100		15708	10	
	5/32	4.2	107	0.84	21	10909	10		12909	100		15709	10	
	3/16	4.5	114	0.94	24	10910	10		12910	100		15710	10	
	7/32	4.9	124	1.03	26	10911	5		12911	50		15711	5	
	1/4	5.6	141	1.13	29	10912	5		12912	50		15712	5	
	5/16	6.0	152	1.25	32	10913	5		12913	50		15713	5	
	3/8	6.8	171	1.38	35	10914	5		12914	50		15714	5	
	7/16	7.5	191	1.50	38	10915	1		12915	25		15715	1	
	1/2	8.3	210	1.63	41	10916	1		12916	25		15716	1	
	9/16	9.0	229	1.75	44	10917	1		12917	10		15717	1	
	5/8	9.8	248	1.88	48	10918	1		12918	10		15718	1	
	3/4	11.3	286	2.13	54	10919	1		12919	5		15719	1	
	7/8	12.8	325	2.37	60	10920	1		-	-		-	-	
	1	14.2	362	2.62	67	10921	1		-	-		-	-	

SINGLE PACKAGING														
PACKAGED														
Singles	SIZE	INCH	MM	INCH	MM	PART#	QTY	LIST EA						
EXTRA LONG Inch	.050	3.1	77	0.53	13	16002	10							
	1/16	3.3	85	0.56	14	16003	10							
	5/64	3.6	92	0.61	15	16004	10							
	3/32	3.9	99	0.65	16	16005	10							
	7/64	4.1	105	0.70	18	16006	10							
	1/8	4.5	114	0.75	19	16007	10							
	9/64	4.8	122	0.80	20	16008	10							
	5/32	5.1	131	0.84	21	16009	10							
	3/16	5.2	132	0.94	24	16010	10							
	7/32	5.6	143	1.03	26	16011	5							
	1/4	6.5	164	1.13	29	16012	5							
	5/16	7.1	180	1.25	32	16013	5							
	3/8	7.8	199	1.38	35	16014	5							

Did you know...?

Bondhus Ball End tips are designed to be the perfect balance between angle and strength. Ball End strength is maximized, while still providing a consistent full 25° working angle.