



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'MPWM-H56-Q'

Your search criteria matched only one product, shown below

MPWM-H56-Q



Push-wing mount is used to secure wires and cables in pre-drilled panels, cabinets or frames. Can be used when only one side of the panel is accessible. The mount is inserted into a pre-drilled hole and locks in place which speeds installation due to the elimination of a screw. Material: 304 stainless steel. Consult factory for additional materials.

- No tapping required
- Used where only one side of the panel is accessible
- Nothing to assemble
- For use with standard, light-heavy and heavy cross section *Pan-Steel*® Ties
- 304 Stainless Steel

	Part Number	MPWMH56-Q
	RoHS Compliancy Status	Compliant
	Part Description	Stainless steel push-winged tie mount. Use with standard, light-heavy and heavy cross section stainless steel ties.
	Height (In.)	.56
	Height (mm)	14.2
	Length (In.)	.98
	Length (mm)	24.7
	Width (In.)	.29
	Width (mm)	7.3
	Hole Diameter (In.)	5/16
	Hole Diameter (mm)	8.0
	Mounting Method	Inserted into pre-drilled hole 5/16 in. (8mm)
	Panel Thickness Range (In.)	.03 – .09
	Panel Thickness Range (mm)	.8 – 2.4
	Pricing Description	Tie Mount, 304 SS, Push Mount, .312" (8mm)
	Min. Order UOM	PC
	Min. Order Qty.	25
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.