

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC  
BDDIST  
39

REVISIONS

| P | LTR | DESCRIPTION  | DATE    | DWN | APVD |
|---|-----|--------------|---------|-----|------|
|   | G   | 0G3B-0317-03 | 24APR03 | TK  | GS   |



1. WIRE RANGE 24-20 AWG.
2. INSULATION RANGE 1.02-2.03[.040-.080] DIA.
3. 0.76 $\mu$ m [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,  
1.27 $\mu$ m [.000050] MIN TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA,  
BOTH OVER 1.27 $\mu$ m [.000050] MIN NICKEL.
4. TIN PLATED.
5. GOLD PLATING PER MIL-G-45204, TIN PER MIL-T-10727  
AND NICKEL PER QQ-N-290.
6. 0.76 $\mu$ m [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,  
1.27 $\mu$ m [.000050] MIN TIN IN LOCALIZED TIN PLATE AREA,  
BOTH OVER 1.27 $\mu$ m [.000050] MIN NICKEL.

|           |        |         |
|-----------|--------|---------|
| 1-66584-0 | 6      | 66594-4 |
| 66584-4   | 3      | 66594-2 |
| 66584-2   | 4      | 66594-1 |
| STRIP REF | FINISH | PART NO |

|                                                                                       |  |                                                           |                                                                              |                       |
|---------------------------------------------------------------------------------------|--|-----------------------------------------------------------|------------------------------------------------------------------------------|-----------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>D.HARDY<br>06/15/94                                | <b>tyco</b><br>Electronics<br>Tyco Electronics Corporation<br>Harrisburg, Pa |                       |
| DIMENSIONS:<br>INCHES                                                                 |  | CHK<br>R.STONE<br>06/22/94                                |                                                                              |                       |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                             |  | APVD<br>G.STEINHAUER<br>06/27/94                          | NAME<br>CONTACT, SOCKET, LOOSE<br>PIECE, TYPE VI, MULTIMATE                  |                       |
| 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± 0.13 [.005]<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± - |  | PRODUCT SPEC<br>—<br>APPLICATION SPEC<br>—<br>WEIGHT<br>— | SIZE<br>A3                                                                   |                       |
| MATERIAL<br>BRS PER MIL-C-50                                                          |  | FINISH<br>5 SEE TABLE                                     | CAGE CODE<br>00779                                                           | DRAWING NO<br>C-66594 |
| CUSTOMER DRAWING                                                                      |  |                                                           | SCALE<br>6:1                                                                 | SHEET<br>1 OF 1       |
|                                                                                       |  |                                                           | REV<br>G                                                                     |                       |