

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[HIGH -Q TOOLS & DMM'S](#) > [MULTIMETERS](#) > [DIGITAL MULTIMETERS](#) >



MINI 3 1/2 DIGIT DMM - 19 RANGES

Order Code: DVM810



Features

- ? automatic polarity indication
- ? voltage measurements: AC 500V and DC 500V max.
- ? current measurements: DC 10A max.
- ? resistance measurements: 2Mohm
- ? diode and transistor (hFE) test
- ? packaging: blister

Specifications

- ? DC voltage: 200m/2000m/20/200/500V
 - ? basic accuracy: $\pm 0.5\%$ ($\pm 0.25\%$ for 200mV range)
 - ? input impedance: -
 - ? maximum input: 500V
- ? AC voltage: 200/500V
 - ? basic accuracy: $\pm 1.2\%$
 - ? input impedance: -
 - ? frequency range: 45-450Hz
 - ? maximum input: 500V
- ? DC current: 200 μ /2000 μ /20m/200m/10A
 - ? basic accuracy: $\pm 1.0\%$ ($\pm 2.0\%$ for 10A range)
 - ? overload protection: 200mA 250V fuse (10A-range is not fuse-protected)
- ? AC current: -
 - ? basic accuracy: -
 - ? overload protection: -
- ? resistance: 200/2000/20k/200k/2000k
 - ? basic accuracy: $\pm 0.8\%$ ($\pm 1.0\%$ for 2000k range)
 - ? overload protection: 220Vrms max. for 15 seconds
- ? capacitance: -
 - ? accuracy: -
- ? inductance: -
 - ? accuracy: -
- ? frequency: -
 - ? basic accuracy: -
 - ? overload protection: -
- ? temperature: -
 - ? basic accuracy: -
- ? overrange: yes
- ? continuity buzzer: -
- ? transistor test: yes
- ? diode test: yes
- ? low-battery indication: yes
- ? maximum display: 3 1/2
- ? LCD display size: 0.5"
- ? ranging mode: manual
- ? data hold: no
- ? backlight: no
- ? dimensions:-
- ? weight (with battery): -
- ? power supply: 12V battery (incl.)
- ? packing: -
- ? accessories: manual / test leads / 1 GP23GA 12V battery
- ? auto power-off: no

Files

- ? [EN- FR- NL- ES- DE](#)

Stock Info

- ? Inner carton: 20
- ? Outer Carton: 100
- ? EAN Barcode: 5410329205317
- ? Packaging: Blister card