





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER 0G3B-0092-05	1/27/05	SS	HW
	D	REVISED PER ECO-16-006378	03NOV2016	RS	MZ
	E	REVISED PER ECR-16-016563	07DEC2016	RS	MZ



RECOMMENDED PANEL CUTOUT

- 1 HOUSING, ADAPTER AND PRESSURE PLATE: NYLON, BLACK.
WIRE ENTRY SEAL: ELASTOMER, SEE TABLE.
PERIPHERAL SEAL: ELASTOMER, GREY.
- 2 CONNECTOR WILL ACCEPT (16) MULTIMATE PIN CONTACTS.

OBSOLETE	W/ 4-40 THREADED INSERT	RED-IRON OXIDE	.065 - .100	STANDARD	-796275-3-
	3.18±0.07 [.150±.003]	YELLOW	.040 - .080	SMALL	796275-2
	3.18±0.07 [.150±.003]	RED-IRON OXIDE	.065 - .100	STANDARD	796275-1
	H	SEAL COLOR	WIRE INSULATION DIAMETER RANGE	INSULATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. McEACHIN 27-JAN-2000		 TE Connectivity													
DIMENSIONS: mm [INCHES]		CHK K. DOWHOWER 27-JAN-2000															
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. DOWHOWER 27-JAN-2000		NAME ASSEMBLY, RECEPTACLE, STANDARD SEX, 17-16, STANDARD OR SMALL INSULATION DIA., SEALED												
			PRODUCT SPEC —														
			APPLICATION SPEC —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO						
	MATERIAL 		FINISH —		WEIGHT —		A2		00779		C=796275		—				
CUSTOMER DRAWING						SCALE		2:1		SHEET		1 of 1		REV		E	