



## 3-1906865-0 Product Details

[Share](#) [Print](#) [Email](#)



3-1906865-0

TE Internal Number: 3-1906865-0



### Fiber Optic Cable Assemblies



[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Cable Assembly
- LC Fiber Optic Cable Connector Type
- Fiber Type = OM1 62.5/125 Micron
- Cable Assembly Type = LC Duplex to LC Duplex
- Multimode

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [C/A,F/O,2F 62.5/125 OFNR 2.0mm ZIPCORD , LC DUPLEX,BO...](#) (PDF, English)

#### Related Products:

- [Tooling](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Cable Assembly
- [Fiber Optic Cable Connector Type](#) = LC
- Cable Assembly Type = LC Duplex to LC Duplex
- Cable Type = Twin Zip

#### Housing Features:

- Fiber Path Configuration = Pair Flipped
- [Flammability Rating Type](#) = OFNR (Riser) Jacket

#### Termination Features:

- [Fiber Type \(Micron\)](#) = OM1 62.5/125
- [Mode](#) = Multimode
- Insertion Loss (dB) = 0.50

#### Configuration Features:

- [Cable Buffering](#) = Tight Buffered
- Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°

#### Body Features:

- Cable Diameter (mm [in]) = 2.00 [.079]
- Number of Fibers = 2
- Cable Color = Orange
- Length (M [ft]) = 30.00 [98.424]
- Connector Color = Beige
- Ferrule Material = Ceramic
- Return Loss (dB) = 0

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Contact Features:

- Boot Body Style - Left = Standard
- Boot Color - Left = Beige/Beige
- Boot Body Style - Right = Standard
- Boot Color - Right = Beige/Beige
- Fibre Channel = No

#### Other:

- Brand = Tyco Electronics

### Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

