


Type Q Right Angle Receptacle Assemblies with Solder Posts and MFBL Contacts



Material

Housing — Glass filled polymer

Contacts — Copper alloy

Related Product Data

DIN Performance Levels — Page 6

Performance Specifications —
Page 8

Mateable Connectors — Pages 14,
50

PC Board Hole Layout — Page 58

Accessories — Pages 68, 69




Technical Documents — Page 74:

DIN Specification 41612

IEC Specification 60603-2

Application Specification
114-9014

Instruction Sheet 408-6784



Standard Size

Number of Positions	Rows Loaded	Dimensions				DIN Level	Part Number
		A	B	C	D		
64	A,B	93.80 3.693	88.90 3.500	78.74 3.100	84.90 3.343	III	174253-2

Note: Locations of MFBL contacts; B1, B32.

Half Size

Number of Positions	Rows Loaded	Dimensions				DIN Level	Part Number
		A	B	C	D		
32	A,B	53.10 2.091	48.24 1.899	38.10 1.500	44.20 1.740	III	174253-1

Note: Locations of MFBL contacts; B1, B16.