

A durable three pin panel plug, with solder lug / spade terminals. Can be mounted above the panel on any thickness of material or below the panel for up to 2,0mm thick material. Suitable for use measuring instruments, SMPS, ITE and OA.


For panel cut-out, use punch number 974-0010 (pull through) or 906-0050 (punch and die).

Weight approximately 10g.

Approvals UL, CSA and TUV.

MATERIAL HOUSING	: Nylon 66, black UL 94 V0
CONTACTS	: Brass, nickel plate
ELECTRICAL	
Voltage Rating	: 250 Vac
Current Rating	: 10 Amps
Insulation Resistance	:1000 MΩ @500 Vac
Withstanding Voltage	: 2000 Vac for 1 minute between line to gnd.
Temperature Range	: -20°C to +80°C

Dimensions



CONVERTED FROM PS0900 ISS1 (02.01.98) IN JAN 2003

DrqNo 520-0010		TITLE MAINS CONNECTOR – PANEL PLUG					ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES			
	ISSUE	2	GENERAL SPECIFICATION FOR 520-0010	CUSTOMER			FILTER REF			
				Aprvd Date 19.02.08	Aprvd By MC	Drwn by BS	Scale: NTS	Sheet 1 / 1		