

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFStud Tie Mou
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) Search Tips

 Text Search: 'TMSTHS11-D0'

Your search criteria matched only one product, shown below

TMSTHS11-D0



- Easily applied to bolts or studs with a light hammer blow or turning of the mount
- Designed for use with cable ties to route and secure cable bundles, air, water and hydraulic lines
- TMSTHS-11-D0 style is designed for use with standard bolt sizes as well as state-of-the-art fasteners such as the Huck BOBTAIL lockbolt

BOBTAIL is a registered trademark of Alcoa Inc.

Part Number	TMSTHS11D0
RoHS Compliancy Status	Compliant
Part Description	Cable Tie Mounts for Threaded Studs.
Material	Impact Modified Weather Resistant Nylon 6.6
Color	Black
Height (In.)	1.10
Height (mm)	27.9
Length (In.)	1.99
Length (mm)	50.5
Width (In.)	1.00
Width (mm)	25.4
CE Compliant	No
Environment	Outdoors
Flammability Rating	HB
Mounting Method	7/16" stud dia. (11mm)
Pricing Description	Cable Tie Mount, .44" (11mm) Stud, Weather Resistant Nylon, BL
Screw Size	7/16 (M10)
Used With Cable Ties	M, I, S, HS, LH, H
Min. Order UOM	PC
Min. Order Qty.	500
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.