

CATALOG LISTING
1PB549-H58
PAGE 1 OF 1
ISSUE
12

REPLACES

PR-5810-T

CHECK

CHECK

REVISIONS

A	C092114
JAK	24 FEB 98
B	203865
CSL	5 SEP 01
C	207683
GLH	19 MAR 03
D	0018502
PM	27 FEB 06



CHECK

CHECK

JAK 24 FEB 98

RASTER

DRAWN




NOTES

- 1 - UNIT INCLUDES CAT. LIST. 11SM23-H58 BASIC SWITCH
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - RECOMMENDED FOR MANUAL OPERATION ONLY
- 4 - FURNISH (1) RED AND (1) WHITE BUTTON UNASSEMBLED
- 5 MOUNTING HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE ----- 17.6 OZ MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT	
OVERTRAVEL ----- .101 APPROX TOTAL TRAVEL ----- .180 MAX	30 VOLTS DC RATING INDUCTIVE ----- SEA LEVEL --- .5 AMP 50,000 FT --- .5 AMP RESISTIVE ----- SEA LEVEL --- 1 AMP 50,000 FT --- 1 AMP MAXIMUM INRUSH ----- 2 AMP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1PB549-H58](#)