


Raised countersunk head machine screws - Recess H



DIN 966
BS 4183
ISO 7047

Materials/Finishes:

Steel 4.8/Zinc & clear
Stainless steel/Self colour
Brass/Self colour

Dimensions

Thread (d)	M2	M2.5	M3	M3.5	M4	M5	M6	M8
H max (BS/DIN)	1.2	1.5	1.65	1.93	2.2	2.5	3	4.5
H max (ISO)	1.2	1.6	1.65	2.35	2.7	2.7	3.3	4.65
recess (BS/DIN)	1	1	1	2	2	2	3	4
recess (ISO)	0	1	1	2	2	2	3	4
D nom (BS)	-	5.5	6.3	7.35	8.4	10	12	16
D nom (DIN)	3.8	4.7	5.6	6.5	7.5	9.2	11	14.5
D nom (ISO)	3.8	4.7	5.5	7.3	8.4	9.3	11.3	15.8

NB: Generally our preferred stock is to DIN - if dimensions are critical to your application you should check with us prior to ordering.

Preferred lengths

All sizes are non-preferred
Please enquire for availability