




CABLE MARKING:


E300060 AWM 2464 VW-1 80°C 300V SR-PVC IEEE-488 26AWG

NOTE: ALL relevant materials are complied with RoHS directive


3	COPPER FOIL 7.5*70mm		2	M583	
	IEEE-488 METALLIZED HOOD		2set	M83	
2	UL2464 12 TWISTED PAIRS 26AWG, ALUM-MYLAR AND COPPER BRAID FOIL FOIL SHIELDING WITH DRIAN WIRE, OD 10.7mm, JACKET SAND WITH A GREENISH CAST GROOVE, DRAWING No. EMAB2612P-731		Xmm	M304	
1	IEEE-488, MALE AND FEMALE, GOLD FLASH ON CONTACTS, BLACK INSULATOR		2set	M83	
No.	DESCRIPTION		Q'TY	Supplier	
APPROVED		Maxxtro®	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm		
CHECKED	HU				
DRAWING	David				
DATE	18/JUL/11	ITEM NO.			3019-3

3019-3


	P1	P2	P3	P4
BROWN	1	1	1	1
BROWN/WHITE	13	13	13	13
RED	2	2	2	2
RED/WHITE	14	14	14	14
ORANGE	3	3	3	3
ORANGE/BLACK	15	15	15	15
PINK	4	4	4	4
PINK/BLACK	16	16	16	16
YELLOW	5	5	5	5
BLACK/WHITE	17	17	17	17
GREEN	6	6	6	6
GREEN/WHITE	18	18	18	18
LIGHT GREEN	7	7	7	7
LIGHT GREEN/BLACK	19	19	19	19
BLUE	8	8	8	8
BLUE/WHITE	20	20	20	20
LIGHT BLUE	9	9	9	9
LIGHT BLUE/BLACK	21	21	21	21
PURPLE	10	10	10	10
PURPLE/WHITE	22	22	22	22
GREY	11	11	11	11
GREY/BLACK	23	23	23	23
SHIELD	12	12	12	12
YELLOW/BLACK	24	24	24	24
SHIELD	SHIELD	SHIELD	SHIELD	SHIELD



LABEL A



LABEL B



LABEL C

ITEM NO.	LENGTH"L"	LENGTH"X"	LABEL
100980	500mm	490mm	LABEL A
100985	1200mm	1190mm	LABEL B
100990	2000mm	1990mm	LABEL C

THE LABEL WILL BE PUT ON THE CENTER OF POLYBAG

No.	DESCRIPTION			Q'TY	Supplier	
APPROVED		Maxxtro®			Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
CHECKED	HU					
DRAWING	David					
DATE	18/JUL/11	ITEM NO.	3019-3			UNIT:mm