

## SUMMARY

### # Wires

Low	4
High	0
Coax	0
Triax	0
Quad	0
Fiber	0
Fluidic	0

Series	P
Termination type	Female print PCB
IP rating	50
Cable Ø	0.00 - 0.00 mm
Matching parts	PAB.M0.4TL.AC39N
Status	active
Alternative part	



*Image is for illustrative purpose only*

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	PK*:
Keying	2 keys (alpha=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PEI (Polyetherimide), black
Cable Fixing	∅ 0 - 0 mm
Variant	N : Black front nut

### Performance

Configuration	1P.M04 : 4 Low Voltage
Insulator	
Rated Current	8 Amps

### Specifications

Contact Type: Print (straight)
Max. Matings: 2000
Contact Dia.: 0.9 mm (0.0354in)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


R (max): 4.5 mOhm  
Test voltage (kV rms) Contact-contact: 1.2  
Air clearance min. (mm) or Creepage distance min. (mm): 1.2

Others

F ret (min): 50 N  
F ret (max): 150 N  
IP Rating: 50

DRAWINGS

Draws



Dimensions

	A	L	N
mm.	19.5	26.5	20.5
in.	0,77	1,04	0,81

RECOMMENDED BY LEMO

Tools

None

Cables

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.