





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

- NOTES: 1. FOR USE WITH PANDUIT MSW50T15-CR4 & MSW50T15-CR6 CONTINUOUS STRAPPING. ^(A)
2. APPLICATION TOOL: BT2MS75, BT2HT
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS
4. UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:
 $.XX = \pm .02$ [.5]
 $.XXX = \pm .010$ [.25]
5. MATERIAL: 304 OR 316 STAINLESS STEEL



							TITLE .500 in [12.70] ENHANCED METAL STRAPPING BUCKLE Ⓑ MSBW50-C4 & MSBW50-C6 CUSTOMER DRAWING					
03A	3/13	JAMB	MIM	RGR0	UPDATED DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01042	ITEM REVISION NAME N41148BS/03		PANDUIT MATERIAL: SEE NOTES DRAWING NUMBER: N41148BS_DC			
02A	10/08	JAMB	SKB	---	ORIG CAD FILE SPEC WAS S41148_02. NOTE 2: APPLICATION TOOL BT1HT REPLACED BY BT2HT	-----	DATASET FILE NAME N41148BS_DC/03A					
02	10/04	JAMB	EJD	JJB	ⒷSTRAPPING PART NO'S. IN TITLE BLOCK CHANGED TO BUCKLE PART NO'S., DUE TO TYPING ERROR	12067	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					
01	9/04	JAMB	EJD	JJB	ⒶVOIDED PART NO'S. MS500X15-TSR & MS500X15-TSR316 & REPLACED BY PART NO'S. MSW50T15-CR4 & MSW50T15-CR6 ON NOTE 1	12052	 THIRD ANGLE PROJECTION					
00	9/03	BRH	EJD	JJB	DRAWING RELEASED	11154						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY BRH	DATE 9/03	CHK EJD	SCALE 2:1	SHT 1 OF 1	SIZE A