



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT PART NUMBER                                                                      | LENGTH  | WEIGHT                               | MOUNTING HOLE DIM. |                 |                 |
|------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|--------------------------------------|--------------------|-----------------|-----------------|
|                                                                                          |                                                                                          |                                      | "X"                | "Y"             | "Z"             |
|  T70B**6 | 72.00 IN $\pm .18$ IN<br>(1828mm $\pm 4.5$ mm)                                           | 3.13 LB/ 72.00 IN<br>(1419g/1828mm)  | 1.87<br>(47.5)     | 4.00<br>(101.6) | 8.00<br>(203.2) |
| T70B**8                                                                                  | 96.00 IN $\pm .18$ IN<br>(2438mm $\pm 4.5$ mm)                                           | 4.17 LB/ 96.00 IN<br>(1891g/2438mm)  | 1.87<br>(47.5)     | 4.00<br>(101.6) | 8.00<br>(203.2) |
| T70B**10                                                                                 | 120.00 IN $\pm .18$ IN<br>(3048mm $\pm 4.5$ mm)                                          | 5.21 LB/ 120.00 IN<br>(2363g/3048mm) | 1.87<br>(47.5)     | 4.00<br>(101.6) | 8.00<br>(203.2) |
| T70B**2                                                                                  | 78.74 IN $\pm .18$ IN<br>(2000mm $\pm 4.5$ mm)                                           | 3.42 LB/ 78.74 IN<br>(1551g/2000mm)  | 1.87<br>(47.5)     | 3.37<br>(85.6)  | 8.00<br>(203.2) |
|  T70B**3 | 118.1 IN $\pm .18$ IN<br>(3000mm $\pm 4.5$ mm)                                           | 5.13 LB/ 118.1 IN<br>(2327g/3000mm)  | 1.87<br>(47.5)     | 3.37<br>(85.6)  | 8.00<br>(203.2) |

 **NOTES:**

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLORS AND/OR PACKAGE QUANTITY.
2. THE T70B IS USED WITH THE T70C RACEWAY COVER.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



CAD FILENAME/LAYERS

D37753BA\_DC\_T70B\_00D.prt

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

**T70 BASE**  
(T70B)  
CUSTOMER DRAWING

|     |          |      |     |                                                                    |          |      |      |     |  |
|-----|----------|------|-----|--------------------------------------------------------------------|----------|------|------|-----|--|
| 3   | 10-05-08 | BOK  | BKR | F. ADDED T70B**3<br>E. REVISED NOTES                               | 37753-03 | RTFI | RTFI |     |  |
| 2   | 5-18-04  | UBN  | BKR | D. REMOVED T70B**3 PART NUMBER                                     | 37753-03 | RGRO | RGRO |     |  |
| -   | -----    | ---  | --- | C. REVISED LENGTH TOLERANCE .18 WAS .13                            | 37753-03 | ---- | ---- |     |  |
| 1   | 1-21-04  | UBN  | BKR | B. ADDED PART NUMBER T70B**6<br>A. REVISED DIMENSION .099 WAS .092 | 37753-03 | RGRO | RGRO |     |  |
| R   | 5-29-01  | REWE | BKR | RELEASED TO PRODUCTION                                             | 37753-03 | HIW  | HIW  |     |  |
| REV | DATE     | BY   | CHK | DESCRIPTION                                                        | ECN      | CHK  | CUST | SUP |  |

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X)  $\pm$  (.XXX)  $\pm$   
(.XX)  $\pm$  .03(.8) ANGLES  $\pm$

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
**REWE**

MAT'L:

SCALE  
**NONE**

DATE  
**5-29-01**

**PVC**

DRAWING NO.  
**37753-03**

DWG  
**A**  
SIZE

CHECKED BY  
**BKR**