


## THB.387.A4A.R

TeePlug 4 pole Screw terminal Plug & Socket, in-line, 7mm to 12mm cable diameter, 4 mm max conductor size IP68 17.5A 450V 2 cable entry, retail pack



### PRODUCT SPECIFICATIONS

|                             |                            |
|-----------------------------|----------------------------|
| Temperature "T" rating      | T125                       |
| Minimum cable diameter (mm) | 7 (5 with reducers fitted) |
| Maximum cable diameter (mm) | 12                         |
| Fixing system               | Cable                      |
| Cable entries               | 2                          |
| Number of poles             | 4                          |
| Terminal type               | Screw                      |
| Body material               | PA66                       |
| Max conductor size (Sq mm)  | 4                          |
| Max current (A)             | 17.5                       |
| Max voltage (V)             | 450                        |
| Minimum temp rating °C      | -40                        |
| Max temp rating °C          | 125                        |
| IP rating                   | 68                         |