



Identification

Part No.

Drawing

Dimensions in mm

Fibre optic cable, double ended,
multi mode, 62.5 μ m

Length: a = 1 m

a = 5 m

a = 10 m

a = 20 m

a = 40 m

a = 50 m

a = 100 m

33 58 211 0010 001

33 58 211 0050 001

33 58 211 0100 001


33 58 211 0200 001

33 58 211 0400 001


33 58 211 0500 001

33 58 211 1000 001

double ended



a = length



Fibre optic cable, single ended,
multi mode, 62.5 μ m

Length: a = 1 m

a = 5 m

a = 10 m

a = 20 m

a = 40 m

a = 50 m

a = 100 m

33 58 111 0010 001

33 58 111 0050 001

33 58 111 0100 001

33 58 111 0200 001


33 58 111 0400 001

33 58 111 0500 001

33 58 111 1000 001

Protection level: IP 65 / IP 67

single ended



a = length

Fibre optic breakout cable,
multi mode, 62.5 μ m

Length: 10 m

Length: 20 m

Length: 100 m

33 58 751 0100 001

33 58 751 0200 001

33 58 751 1000 001



PUR jacket

2-fibre multi mode 62.5 μ m

Outer diameter: 7 mm

Min. bending radius:
Installation: 10.5 cm

Operating: 7.0 cm