




MT-100 & TP-100 Handpiece & Tips


MT-100/TP-100

HANDPIECE	DESCRIPTION	PART NUMBERS
	MT-100 HeatWise/TempWise Handpiece	6010-0140-P1
	MT-100 HeatWise/TempWiseTip & Tool Stand Kit (Includes MT-100 and Stand)	6993-0243-P1
	MT-100 Handpiece IntelliHeat	6010-0148-P1
	MT-100 Handpiece Kit IntelliHeat	6993-0264-P1
	TP-100 Handpiece IntelliHeat	6010-0158-P1
	TP-100 Handpiece Kit IntelliHeat	6993-0280-P1
	Cleaning Sponge, Tip & Tool Stands (SX, PS, SP)	4021-0008-P3
	MT-100 & TP-100 Tip & Tool Stand (Available November 07)	6019-0080-P1
	Soft Grip	1119-0165-P2
	Green Comfort grip & green Handpiece Insert for MT-100 Tip & Tool Stand	6993-0284-P1
	Replacement Green Comfort Grips for MT-100, pack of 5	1119-0177-P2
	Green replacement handpiece insert for	
	MT-100/TP-100 Green, Lead Free Handpiece Insert (Before Nov 07)	1257-0323-G-P1
	MT-100/TP-100 Green, Lead Free Handpiece Cubby (After 11-07)	6019-0080-G-P1
	MT-100/TP-100 Green, Lead Free Handpiece Insert (After 11-07)	1257-0383-G-P1

MT-100 Surface Mount Removal Tips

TIP	COMPONENT TYPE	DIMENSION A	DIMENSION B	PART NUMBERS
	Chip (fig.A)	0.2mm (.008")	0.2mm (.008")	1124-1001-P1
	Chip, SOT (fig.B)	0.7mm (.03")	0.5mm (.02")	1124-1002-P1
	Chip, SOT (fig.B)	0.7mm (.03")	1mm (.04")	1124-1003-P1
	Chip, SOT (fig.B)	0.7mm (.03")	2mm (.08")	1124-1004-P1
	SOIC, SOT, TSOPS (fig.C)	0.7 mm (.03")	6mm (.24")	1124-1005-P1
	SOIC, SOT, TSOPS (fig.C)	0.7mm (.03")	8mm (.31")	1124-1006-P1
	SOIC, SOT, TSOPS (fig.C)	0.7mm (.03")	10mm (.39")	1124-1007-P1
	SOIC, SOT, TSOPS (fig.C)	0.7mm (.03")	13mm (.51")	1124-1008-P1
	SOIC, SOT, TSOPS (fig.C)	0.7mm (.03")	18mm (.74")	1124-1009-P1
	SOIC, SOT, TSOPS (fig.C)	0.7mm (.03")	28mm (1.09")	1124-1010-P1

TP-100 Surface Mount Removal Tips

TIP	TYPE	LEAD COUNT	SIZE-A	SIZE-B	HEIGHT	FOOTPRINT	PART NUMBERS
	LQFP/TQFP	80	12mm (.472")	12mm (.472")	1.4mm	2.0mm	1124-2001-P1
	LQFP/TQFP	64, 80, 100, 120, 128, 168	14mm (.551")	14mm (.551")	1.4mm	2.0mm	1124-2002-P1
	LQFP/TQFP	128, 144, 160, 176	20mm (.788")	20mm (.788")	1.4mm	2.0mm	1124-2003-P1
	LQFP/TQFP	176, 216	24mm (.945")	24mm (.945")	1.4mm	2.0mm	1124-2004-P1
	LQFP/TQFP	208, 256	28mm (1.10")	28mm (1.10")	1.4mm	2.0mm	1124-2005-P1
	QFP	52, 64, 80, 100	14mm (.551")	14mm (.551")	2.7mm	3.2mm	1124-2006-P1
	QFP	52, 64, 80, 100	14mm (.551")	14mm (.551")	2.7mm	3.9mm	1124-2007-P1
	QFP	64, 80, 100, 128	14mm (.551")	20mm (.788")	2.7mm	3.2mm	1124-2008-P1
	QFP	64, 80, 100, 128	14mm (.551")	20mm (.788")	2.7mm	3.9mm	1124-2009-P1
	QFP	120, 128, 144, 160, 208	28mm (1.10")	28mm (1.10")	3.4mm	2.6/3.2mm	1124-2010-P1
	QFP	160	28mm (1.10")	28mm (1.10")	3.4mm	3.9mm	1124-2011-P1