


OVERVIEW PRODUCT

From 250x200x150 to 1200x1000x400 you have more than 45 sizes to choose...



1• Transparent tempered glass door and fully watertight, maintaining IP-66 protection.



2• Front rain gutter avoids the entry of water, oil or liquids which ensures high degree of protection and protects the inside surface when opening the door.



3• A complete range of mounting plates suitable for most types of installations.

The fullest variety of accessories in the market.



4• Wall fixing brackets fixed from the outside and can be placed both horizontally or vertically. Not included as standard supply.



5• Embedded cable gland plate and entrance, leveled with the base, with a neoprene seal.

Insulated cable gland plates with pre-punched holes for easy cable entry available as accessory.




6• Foamed-in polyurethane gasket guarantees watertightness for years.

7• Perforated door reinforcement profiles allowing fixing of equipment in up to 500 mm high enclosures.



8• Built in standard double bar locking system and three points locking for two doors enclosures and 1200 mm high enclosures. Different lock transformations available.



9• Two M6x15 welded earth studs on the back and one M6x15 stud on the door.

10• Easily reversible door, fitted with two or three invisible hinges allowing 120° opening.



11• Back of enclosure with four M8x15 welded studs with built-in spacers for fixing of mounting plate and adjustable support.

12• Wall fixing holes sealed with plastic plugs to assure the protection degree.



13• Depth adjustable support with positions every 12,5 mm. Front part drilled to M6 ø in order to fit mounting plates, internal doors, etc...

WALL MOUNTING STEEL ENCLOSURES SYSTEM IP-66 (CEI-529)

Metal enclosures made from a continuous length of sheet steel double folded at the front, with back welded to the frame. Both externally and internally protected with polyester epoxy resin grey paint to RAL-7032 texturized.



- IP-66 for one door enclosures.
- IP-55 for two doors enclosures.
- series **CRN....KT** with transparent security glass door.
- welded studs on the back for direct fixing of mounting plate or other accessories.
- perforated door reinforcement profiles allowing fixing of equipment.
- concealed and easily removable hinges allowing over 120° door opening.
- foamed-in polyurethane gasket and front rain gutter ensures high degree of protection.
- accessories not included as standard supply.

dimensions (mm.)

FIG. 1




FIG. 2




FIG. 3










FIG. 4



* All glazed door enclosures type KT are without door reinforcement profiles.

** for 1200 mm. width

References and details of enclosures

external dimensions (mm)			enclosures					metal		mounting plates						
height (A)	width (B)	depth (C)	reference	reference with glazed door	fig.	flange opening type	weight* (Kg)	metal	insul.	perf.	univer.					
250	200	150	CRN-2520/150	-	1	O	3,2	MM-2520	MB-2520	MF-2520	MR-2520	-	-	-	-	-
300	250	150	CRN-3025/150	CRN-3025/150KT	1	A	4,2	MM-3025	MB-3025	MF-3025	MR-3025	-	-	-	-	-
300	250	200	CRN-3025/200	CRN-3025/200KT	1	A	4,9	MM-3025	MB-3025	MF-3025	MR-3025	SDCR-200	-	-	-	-
300	300	150	CRN-33/150	CRN-33/150KT	1	B	5	MM-33	MB-33	MF-33	MR-33	-	-	-	-	-
300	300	200	CRN-33/200	CRN-33/200KT	1	B	6	MM-33	MB-33	MF-33	MR-33	SDCR-200	-	-	-	-
300	400	200	CRN-34/200	CRN-34/200KT	1	C	6,4	MM-34	MB-34	MF-34	MR-34	SDCR-200	-	-	-	-
400	300	150	CRN-43/150	CRN-43/150KT	1	B	6	MM-43	MB-43	MF-43	MR-43	-	DLM-24	DLA-24	-	PIN-43
400	300	200	CRN-43/200	CRN-43/200KT	1	B	6,8	MM-43	MB-43	MF-43	MR-43	SDCR-200	DLM-24	DLA-24	-	PIN-43
400	400	200	CRN-44/200	CRN-44/200KT	1	C	8	MM-44	MB-44	MF-44	MR-44	SDCR-200	-	-	-	-
400	600	250	CRN-46/250	CRN-46/250KT	1	D	10	MM-46	MB-46	MF-46	MR-46	SDCR-250	-	-	BRF-8/CRN BRP-7/CRN	-
400	600	300	CRN-46/300	CRN-46/300KT	1	D	11,2	MM-46	MB-46	MF-46	MR-46	SDCR-300	-	-	BRF-8/CRN BRP-7/CRN	-
500	400	150	CRN-54/150	CRN-54/150KT	2	B	8,7	MM-54	MB-54	MF-54	MR-54	-	DLM-48	DLA-48	-	-
500	400	200	CRN-54/200	CRN-54/200KT	2	C	9,8	MM-54	MB-54	MF-54	MR-54	SDCR-200	DLM-48	DLA-48	-	PIN-54
500	400	250	CRN-54/250	CRN-54/250KT	2	C	11	MM-54	MB-54	MF-54	MR-54	SDCR-250	DLM-48	DLA-48	-	-
500	500	250	CRN-55/250	CRN-55/250KT	2	D	12,8	MM-55	MB-55	MF-55	MR-55	SDCR-250	-	DLA-48	-	-
600	400	150	CRN-64/150	CRN-64/150KT	2	B	9,3	MM-64	MB-64	MF-64	MR-64	-	DLM-48P	DLA-48P	-	PIN-64
600	400	200	CRN-64/200	CRN-64/200KT	2	C	10,8	MM-64	MB-64	MF-64	MR-64	SDCR-200	DLM-48P	DLA-48P	-	PIN-64
600	400	250	CRN-64/250	CRN-64/250KT	2	C	12,3	MM-64	MB-64	MF-64	MR-64	SDCR-250	DLM-48P	DLA-48P	-	PIN-64
600	500	150	CRN-65/150	CRN-65/150KT	2	B	11,3	MM-65	MB-65	MF-65	MR-65	-	-	-	-	-
600	500	200	CRN-65/200	CRN-65/200KT	2	D	14,3	MM-65	MB-65	MF-65	MR-65	SDCR-200	-	-	-	-
600	500	250	CRN-65/250	CRN-65/250KT	2	D	16,3	MM-65	MB-65	MF-65	MR-65	SDCR-250	-	-	-	-
600	600	200	CRN-66/200	CRN-66/200KT	2	D	15,5	MM-66	MB-66	MF-66	MR-66	SDCR-200	DLM-84P	-	BRF-12/CRN BRP-11/CRN	-
600	600	250	CRN-66/250	CRN-66/250KT	2	D	18,2	MM-66	MB-66	MF-66	MR-66	SDCR-250	DLM-84P	-	BRF-12/CRN BRP-11/CRN	-
600	600	300	CRN-66/300	CRN-66/300KT	2	D	19,8	MM-66	MB-66	MF-66	MR-66	SDCR-300	DLM-84P	-	BRF-12/CRN BRP-11/CRN	-
600	800	300	CRN-68/300	CRN-68/300KT	2	E	26	MM-68	MB-68	MF-68	MR-68	SDCR-300	-	-	-	-
700	500	200	CRN-75/200	CRN-75/200KT	2	D	17,3	MM-75	MB-75	MF-75	MR-75	SDCR-200	DLM-66 DLM-88	DLA-66 DLA-88	-	PIN-75
700	500	250	CRN-75/250	CRN-75/250KT	2	D	19,3	MM-75	MB-75	MF-75	MR-75	SDCR-250	DLM-66 DLM-88	DLA-66 DLA-88	-	PIN-75
800	600	200	CRN-86/200	CRN-86/200KT	2	D	21,8	MM-86	MB-86	MF-86	MR-86	SDCR-200	DLM-84 DLM-112	DLA-84 DLA-112	BRF-17/CRN BRP-16/CRN	PIN-86
800	600	250	CRN-86/250	CRN-86/250KT	2	D	24,8	MM-86	MB-86	MF-86	MR-86	SDCR-250	DLM-84 DLM-112	DLA-84 DLA-112	BRF-17/CRN BRP-16/CRN	PIN-86
800	600	300	CRN-86/300	CRN-86/300KT	2	D	26,3	MM-86	MB-86	MF-86	MR-86	SDCR-300	DLM-84 DLM-112	DLA-84 DLA-112	BRF-17/CRN BRP-16/CRN	PIN-86
800	600	400	CRN-86/400	CRN-86/400KT	2	D	31	MM-86	MB-86	MF-86	MR-86	SDCR-400	DLM-84 DLM-112	DLA-84 DLA-112	BRF-17/CRN BRP-16/CRN	PIN-86
800	800	200	CRN-88/200	CRN-88/200KT	2	E	29,5	MM-88	MB-88	MF-88	MR-88	SDCR-200	-	-	-	-
800	800	300	CRN-88/300	CRN-88/300KT	2	E	32,5	MM-88	MB-88	MF-88	MR-88	SDCR-300	-	-	-	-
800	1000	300	CRN-810/300**	-	4	E	37	MM-810	MB-810	MF-810	MR-810	SDCR-300	-	-	-	-
1000	600	250	CRN-106/250	CRN-106/250KT	2	D	28,4	MM-106	MB-106	MF-106	MR-106	SDCR-250	DLM-168	-	BRF-21/CRN BRP-20/CRN	PIN-106
1000	600	300	CRN-106/300	CRN-106/300KT	2	D	30,6	MM-106	MB-106	MF-106	MR-106	SDCR-300	DLM-168	-	BRF-21/CRN BRP-20/CRN	PIN-106
1000	800	250	CRN-108/250	CRN-108/250KT	2	E	34,5	MM-108	MB-108	MF-108	MR-108	SDCR-250	DLM-240	DLA-240	BRP-20/CRN-800	PIN-108
1000	800	300	CRN-108/300	CRN-108/300KT	2	E	37,4	MM-108	MB-108	MF-108	MR-108	SDCR-300	DLM-240	DLA-240	BRP-20/CRN-800	PIN-108
1000	800	400	CRN-108/400	CRN-108/400KT	2	E	43	MM-108	MB-108	MF-108	MR-108	SDCR-400	DLM-240	DLA-240	BRP-20/CRN-800	PIN-108
1000	1000	300	CRN-1010/300**	CRN-1010/300KT**	4/3	E	46,7	MM-1010	MB-1010	MF-1010	MR-1010	SDCR-300	-	-	-	-
1000	1200	300	CRN-1012/300**	-	4	E	41	MM-1012	MB-1012	MF-1012	MR-1012	SDCR-300	-	-	-	-
1200	800	300	CRN-128/300**	CRN-128/300KT**	3	E	44,8	MM-128	MB-128	MF-128	MR-128	SDCR-300	-	-	BRP-25/CRN-800	PIN-128
1200	800	400	CRN-128/400**	CRN-128/400KT**	3	E	50	MM-128	MB-128	MF-128	MR-128	SDCR-400	-	-	BRP-25/CRN-800	PIN-128
1200	1000	300	CRN-1210/300**	-	4	E	53,4	MM-1210	MB-1210	MF-1210	MR-1210	SDCR-300	-	-	-	-
1200	1000	400	CRN-1210/400**	CRN-1210/400KT**	4	E	53,4	MM-1210	MB-1210	MF-1210	MR-1210	SDCR-400	-	-	-	-

* Weight of enclosures with plain door. ** Enclosures with three point locking system.