



Fluke in Hungary

FLUKE[Home](#)[Products](#)[Applications](#)[Distributors](#)[News](#)[Support](#)
Search by model[Manual](#)[Product registration](#)[Accessories](#) > [Industrial test leads, probes and clips](#) >

VPS101 – Voltage Probe Set, 1:1, one black



Double insulated safety design probe for ScopeMeter 190 series

Each probe set includes:

- 300 V CAT III rated 1:1 Voltage Probe
- Hook Clip for Probe Tip
- 4-mm Test Pin for Probe
- Ground Lead with Hook Clip
- Ground Lead with Mini Alligator
- Insulation Sleeve
- 30 V CAT II rated Ground Spring for P

Specification:

- Attenuation: 1x
- Bandwidth: 30 MHz
- Max. Input Voltage: 300 V CAT II
- Max. Voltage to ground: 300 V CAT II
EN61010-031
- Input Resistance: 1 M Ω
- Input Capacitance: 42 pF + input capacitance of instrument
- Cable Length: 1.2 m



*Prices are suggested resale prices (excl. VAT)

© 1995 - 2008 Fluke Corporation