



Series X508 Single and Dual Row Collet Sockets with Wire Wrap Pins

FEATURES:

- Aries collet sockets are available in single or dual rows.
- Cuttable to the number of pins desired to fit the application.
- Side-to-side and end-to-end stackable.

SPECIFICATIONS:

- Body material is black UL 94V-0 Nylon 4/6.
- Pin body is Brass Alloy 360 1/2 hard per UNS C36000 ASTM-B16-00.
- Pin body plating is either $10\ \mu$ [.25 μ m] min. Gold per MIL-G-45204 or $200\ \mu$ [5.08 μ m] min. 93/7 Tin/Lead per ASTM B545 or $200\ \mu$ [5.08 μ m] min. Tin per ASTM B545 Type 1 over $100\ \mu$ [2.54 μ m] min. Nickel per SAE-AMS-QQ-N-290.
- 4-fingered collet contact is Beryllium Copper Alloy per UNS C17200 ASTM-B194-01.
- Contact plating is either $200\ \mu$ [5.08 μ m] min. 93/7 Tin/Lead per ASTM B545 or $200\ \mu$ [5.08 μ m] min. Tin per ASTM B545 Type 1 or $10\ \mu$ [.25 μ m] min. Gold per MIL-G-45204 over $50\ \mu$ [1.27 μ m] min. Nickel per SAE-AMS-QQ-N-290.
- Contact current rating=3 Amps.
- Operating Temp. = -67°F to 221°F [-55°C to 105°C] Tin
= -67°F to 257°F [-55°C to 125°C] Gold
- Insertion Force=180 grams/pin; Withdrawal Force=90 grams/pin; Normal Force=140 grams/pin; based on a .018 [.46] dia. test lead.
- Accepts leads .015-.025 [.38-.64] in diameter, .110-.160 [2.79-4.06] long.


MOUNTING CONSIDERATIONS:

- Suggested PCB hole size= $.045 \pm .002$ [1.14 ± .05] dia.

ALL DIMENSIONS: INCHES [MILLIMETERS]


"A"=(NO. OF PINS PER ROW) X .100 [2.54]

"B"=(NO. OF PINS PER ROW - 1) X .100 [2.54]



All tolerances $\pm .005$ [.13] unless otherwise specified

Consult Data Sheet No. 12020
for Series X518 Collet Sockets
with solder tail pins.



Note: Aries specializes in custom design and production. In addition to the standard products shown on this page, special materials, platings, sizes, and configurations can be furnished, depending on quantities. Aries reserves the right to change product specifications without notice.

ORDERING INFORMATION


XX-X508-XXXX

No. of pins:
Single row: 1-40 pins
Dual row: 2-40 pins

Series:
0=Single row
1=Dual row

Plating:
0=Gold collet/Tin shell
0TL=Gold collet/Tin/Lead shell
1=Gold collet/Gold shell

2=2 level wire wrap
3=3 level wire wrap



2 LEVEL 3 LEVEL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aries:](#)

[12-1508-30](#) [22-1508-30](#)