


CATALOG LISTING
14XE1-12
PAGE 1 OF 1
RELEASE NO. PR-13596
CHECK
REPLACES
ISSUE
M
2
REVISIONS
A C094274
DLM
16 MAR 99
CHECK
16 MAR 99
JAF
CHECK
16 MAR 99
DLM
16 MAR 99
FORMTEK
DRAWN




NOTES

- 1 MOUNTING HOLES WILL ACCEPT $.087$ MAX DIA PINS OR SCREWS ON $.188 \pm .002$ CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS $.16$ OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS 3.7 OZ MAX
- 4 - FOR USE IN TEMPERATURE RANGE FROM -65°F TO $+300^{\circ}\text{F}$

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	DO NOT SCALE PRINT
OPERATING FORCE - — — — — 9 OZ MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE - — — — — 2 OZ MIN	28 VOLTS DC RATING	ONE PLACE $(.0)$ $\pm .030$	
PRETRAVEL - — — — — $.004$ MIN	INDUCTIVE — — — SEA LEVEL — — — 4 AMP	TWO PLACE $(.00)$ $\pm .015$	
DIFFERENTIAL TRAVEL - — — — — $.005$ MAX	50,000 FT — — — 2.5 AMP	THREE PLACE $(.000)$ $\pm .005$	
OVERTRAVEL - — — — — $.004$ MIN	RESISTIVE — — — SEA LEVEL — — — 7 AMP	ANGLES $\pm$	
	50,000 FT — — — 7 AMP	WEIGHT $\triangle 3$	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[14XE1-12](#)