






- 1 HOUSING: GLASS FILLED POLYESTER; COLOR: BLACK.
- 2 CONTACT: PHOSPHOR BRONZE.
- 3 NICKEL UNDERPLATE: 0.00127 [± 0.000050] MIN - ALL OVER.
- 4 MATTE TIN PLATE: 0.00254 [± 0.000100] MIN - SOLDER POSTS.
- 5 GOLD PLATE: 0.00076 [± 0.000030] MIN - CONTACT AREA.
- 6 NICKEL PLATE PER MIL-G-45204. GOLD PLATE PER QQ-N-290.
- AMP PART NUMBER, DATE CODE, AND CSA LOGO ARE MARKED IN APPROXIMATE AREA SHOWN, EITHER SIDE.

141.60 [5.575]	148.46 [5.845]	124.46 [4.900]	129.54 [5.100]	130.81 [5.150]	133.60 [5.260]	49	50	5530826-3
F	E	D	C	B	A	X	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AL FRANTUM 14 JUN 05		Tyco Electronics Corporation Harriaburg, Pa 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ 0.13 [.005] 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ -		NAME PRODUCT SPEC 108-9039 APPLICATION SPEC	
MATERIAL		FINISH		RESTRICTED TO	
3/4/5/6		3/4/5/6		A1 00779 C=5530826	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1 REV A	