


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	110	Vdc
OPERATING VOLTAGE RANGE	60 ~ 150	Vdc
RATED CURRENT (MAX)	45	mA
MINIMUM SPL @ 10 cm	92	dBA
RESONANT FREQUENCY	60	Hz
TONE OR PULSE RATE	CONTINUOUS	0 PULSE PER SECOND
OPERATING TEMPERATURE	-20 ~ +60	°C
STORAGE TEMPERATURE	-30 ~ +70	°C
HOUSING MATERIAL	ABS	-
TERMINAL MATERIAL	WIRE LEAD	-
WEIGHT	32	grams


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	05/02/02	
A	REVISED TO NEW TEMPLATE	10/25/05	B.R.



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AI-298.DWG

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.		 projects [®] unlimited Dayton, Ohio									
<table border="1"> <tr> <td>APPROVALS</td> <td>DATE</td> </tr> <tr> <td>DRAWN <i>RABL</i></td> <td>05/02</td> </tr> <tr> <td>CHECKED <i>X.X.</i></td> <td><i>x/xx</i></td> </tr> <tr> <td>APPROVED <i>S.J.</i></td> <td>05/07/02</td> </tr> </table>		APPROVALS	DATE	DRAWN <i>RABL</i>	05/02	CHECKED <i>X.X.</i>	<i>x/xx</i>	APPROVED <i>S.J.</i>	05/07/02	INDICATOR	
APPROVALS	DATE										
DRAWN <i>RABL</i>	05/02										
CHECKED <i>X.X.</i>	<i>x/xx</i>										
APPROVED <i>S.J.</i>	05/07/02										
DO NOT SCALE DRAWING		SIZE A	DRAWING NO. AI-298								
		SCALE: N.T.S.	SHEET 1 OF 1								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-298](#)