

Marine Products Receptacles

Inside the Boat



HBL213MI



CRO15



CRO20I



HBL5251



HBL5361I



HBL52CM62I



HBL8200ILI



HBL6079

Style Line® Receptacles

- High-Impact nylon face resists breaking, chipping and cracking.
- Will accept locking fork terminal to comply with ABYC standards.
- Available in 4 colors for any decor with matching wall plates.
- Smooth, high-gloss finish for rich appearance.

Style Line Series

Description	Catalog Numbers
15A 125V brown duplex receptacle. See note A.	HBL2132M*
Same as #HBL2132M except ivory. See note A.	HBL2132MI
Same as #HBL2132M except white. See note A.	HBL2132MW*
Same as #HBL2132M except gray. See note A.	HBL2132MGY

Commercial Series

Description	Catalog Numbers
15A 125V brown duplex receptacle. See note A.	CRO15
Same as #CRO15 except gray. See note A.	CRO15GRY*
Same as #CRO15 except ivory. See note A.	CRO15I*
20A 125V brown duplex receptacle. See note A.	CRO20*
Same as #CRO20 except black. See note A.	CRO20BLK*
Same as #CRO20 except gray. See note A.	CRO20GRY*
Same as #CRO20 except ivory. See note A.	CRO20I
Same as #CRO20 except white. See note A.	CRO20WHI*
15A 125V brown single receptacle.	HBL5251
Same as #HBL5251 except ivory.	HBL5251I*
20A 125V brown single receptacle.	HBL5361*
Same as #HBL5361 except ivory.	HBL5361I

Corrosion Resistant Series

Description	Catalog Numbers
15A 125V yellow corrosion resistant duplex receptacle. <i>Use where salt or other corrosive elements are a problem.</i>	HBL52CM62*
Same as #HBL52CM62 except ivory.	HBL52CM62I

Special Application Series

Description	Catalog Numbers
Illuminated receptacle 15A 125V grounding. A high quality receptacle with something extra: an illuminated face. Ideal for use in halls or as a gentle night light.	HBL8200ILI

Outlet Box

Description	Catalog Numbers
Plastic switch/receptacle box. Measures 3 9/32" x 2 3/16" x 2 1/2" (83.3 x 55.6 x 63.5) deep. For mounting in walls without studs. A support strap is provided which pulls box tightly against back side of wall.	HBL6079

Note: Will accept locking fork terminal to comply with ABYC standards.

*Not shown.

Marine Products

Switches & Weatherproof Switch Plates

15 and 20 Ampere, 120-277 Volt

**Commercial Series**

Description	Catalog Numbers
Single-pole toggle switch for controlling AC load from one point, brown handle. See note A.	CS115*
Same as #CS115 except gray handle. See note A.	CS115GY*
Same as #CS115 except ivory handle. See note A.	CS115I
Same as #CS115 except office white handle. See note A.	CS115OW*
Same as #CS115 except white handle. See note A.	CS115W*
Three-way toggle switch for controlling AC load from two points, brown handle. See note A.	CS315*
Same as #CS315 except gray handle. See note A.	CS315GY*
Same as #CS315 except ivory handle. See note A.	CS315I*
Same as #CS315 except office white handle. See note A.	CS315OW*
Same as #CS315 except white handle. See note A.	CS315W*



CS115I



HBL1221IL



HBL1221PL

Special Application Series


Description	Catalog Numbers
20A 120V toggle switch with neon lamp set in ivory handle. Handle illuminates when switch is in "OFF" position.	HBL1221IL
20A 120V three-way toggle switch with illuminated ivory handle for controlling AC load from two points. Handle illuminates when "OFF."	HBL1223IL*
20A 120V single-pole toggle switch with neon lamp set in clear red handle. Handle illuminates when switch is "ON." Serves as instant reminder that current is flowing to an appliance.	HBL1221PL
20A 120V three-way toggle switch for controlling AC load from two points. Red handle illuminates when "ON."	HBL1223PL*
Single-pole PresSwitch® for controlling AC load from one point. Switch activated brown button.	HBL1281
Same as #HBL1281 except ivory button.	HBL1281I*
Three-way PresSwitch® for controlling AC load from two points. Switch activated brown button.	HBL1283†
Same as #HBL1283 except ivory button.	HBL1283I††
Yellow neoprene weatherproof plate for use only with PresSwitches. PresSwitch button is activated when bubble is pressed. Not CSA.	HBL17CM50†
Clear silicone rubber weatherproof bubble plate for use with all AC toggle switches and PresSwitches. Also ideal for use with lighted handle toggle switches. Not CSA.	HBL1795



HBL1281



HBL1283



HBL17CM50



HBL1795

Outlet Box

Description	Catalog Numbers
Plastic switch/receptacle box. Measures 3 7/32" x 2 3/16" x 2 1/2" (83.3 x 55.6 x 63.5) deep. For mounting in walls without studs. A support strap is provided which pulls box tightly against back side of wall. Not CSA.	HBL6079

Note: Will accept locking fork terminal to comply with ABYC standards.

*Not shown.



†Not UL Listed.



HBL6079

Marine Products

Wall Plates, TV & Phone Plates*Inside the Boat*

		Smooth High Impact Nylon				Smooth Metal	
		Color	Gangs	Standard Series	Mid-Size Series	Brass	Stainless Steel
		Ivory	One	P1	PJ1	B1	S1
		Gray	One	P1G	—	—	—
		White	One	P1W	PJ1W	—	—
		Brown	One	P1X	PJ1X	—	—
		Ivory	Two	P2	PJ2	B2	S2
		Gray	Two	P2G	—	—	—
		White	Two	P2W	PJ2W	—	—
		Brown	Two	P2X	PJ2X	—	—
P1	P2						
		Ivory	One	P8	PJ8	B8	S8
		Gray	One	P8G	—	—	—
		White	One	P8W	PJ8W	—	—
		Brown	One	P8X	PJ8X	—	—
		Ivory	Two	P82	PJ82	B82	S82
		Gray	Two	P82G	—	—	—
		White	Two	P82W	PJ82W	—	—
		Brown	Two	P82X	PJ82X	—	—
P8	P82						
		Ivory	One	HPS1I	PJ26	B26	S26
		Gray	One	HPS1G	PJ26G	—	—
		White	One	HPS1WA	—	—	—
		Brown	One	HPS1	PJ26X	—	—
		Ivory	Two	HPS2I	PJ262	B262	S262
		Gray	Two	HPS2G	—	—	—
		White	Two	HPS2WA	—	—	—
		Brown	Two	HPS2	PJ262X	—	—
HSP1	HSP2						
		Ivory	One	P7	PJ7	B7	S7
		Gray	One	P7G	—	—	—
		White	One	P7W	PJ7W	—	—
		Brown	One	P7X	PJ7X	—	—
P7							
		Ivory	Two	P18	PJ18	B18	S18
		Gray	Two	P18G	—	—	—
		White	Two	P18W	PJ18W	—	—
		Brown	Two	P18X	PJ18X	—	—
P18							
		Ivory	Two	—	PJ126	—	S126
		White	Two	—	PJ126WA	—	—
		Brown	Two	—	PJ126X	—	—
PJ126							
		Ivory	One	P14	—	—	S13
		Gray	One	P14G	—	—	—
		White	One	P14W	—	—	—
		Brown	One	P14X	—	—	—
P14							
	6 Conductor Telephone Jack	Ivory	One	—	PJ216	—	—
		Brown	One	—	PJ216X	—	—
PJ216							
	(Two openings) TV plate with RG59 Connector.	Ivory	One	—	PJ212	—	—
PJ212 (Not CSA)							

