






Wires loading


Pair no.	Pin	Wire	Pair no.	Pin	Wire
1	1	blue	13	24	green
	6	white		31	red
2	2	blue	14	25	green
	3	yellow		26	black
3	4	blue	15	27	green
	5	red		42	white/blue
4	7	blue	16	28	brown
	8	black		29	white
5	9	blue	17	32	brown
	12	white/blue		33	yellow
6	10	orange	18	34	brown
	11	white		35	red
7	13	orange	19	36	brown
	14	yellow		39	black
8	15	orange	20	37	brown
	30	red		38	white/blue
9	16	orange	21	40	grey
	21	black		41	white
10	17	orange	22	43	grey
	18	white/blue		44	yellow
11	19	green	23		not connected (grey/red)
	20	white			
12	22	green	24		not connected (grey/black)
	23	yellow			
		Cu-foil	shield		



-Temperature range: -5°C ...+80°C

For Information Only
-won't be replaced when changed-

4	Cable 24AWG26	33 56 221 005 0001	5 m
3	Cable 24AWG26	33 56 221 002 0001	2 m
2	Cable 24AWG26	33 56 221 001 0001	1 m
1	Cable 24AWG26	33 56 224 500 0001	0.5 m
Cont No.	Type of cable	Part-No.	Dim. a

 All Dimensions in mm Original Size DIN A 3	Techn. Character.	Nicht tolerierte Maß/Free size tolerances
	Dat.	Name
	Maßstab/Scale	
	Detail.	02.06.09 MS
	Insp.	02.06.09 RA
	Stand.	
	2:1	
DRS509B 12.02.10 MS	HARTING Electronics GmbH & Co. KG	TB 33 56 22x xxx 0001
Mod. Dat. Name	D-32339 ESPELKAMP	Sub.
		Blatt/ page