




Dimensions: mm (In)




TERMINAL TYPES




Quick connect terminal 187 series (D)




Quick Connect Terminal




OPERATING CHARACTERISTICS



MOUNTING HOLES



CONTACT CONFIGURATION



Mechanical Specifications:

- Operating Frequency: 300 operations/min.
- Life: 5,000,000~10,000,000 operations

Electrical Specifications:

- Rating: 0.1A/125/250VAC
- Insulation Resistance (at 500VDC): 10MΩ min.
- Dielectric Strength: 1,000VAC RMS (50-60HZ)
- Contact Resistance (Initial): 30mΩ, 100mΩ max.
- Operating Frequency: 10-30 operations/min.
- Life: 6,000~100,000 operations min.

Operating Characteristics:

- OF Max. (g): 75
- OP (mm): 14.7±0.5
- PT Max. (mm): 1.20
- OT Min. (mm): 0.80
- MD Max. (mm): 0.25

Miniature Snap Switch
SNS21-P1-075XX-Q21

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-21-P1-075XX-Q21](#)