

EXTERNAL DRIVE PIEZO ELECTRIC



ROHS COMPLIANT

PART NUMBER:
BRP1708P-30

SPECIFICATIONS:

RATED VOLTAGE:	30 Vp-p VD
SOUND OUTPUT LEVEL:	95dB @30CM
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	4500 $\pm$ 500 Hz
OPERATING TEMPERATURE:	-20 TO +60 °C
ELECTROSTATIC CAPACITY:	8,000 $\pm$ 30%
FRAME DIAMETER:	17.0 mm
FRAME DEPTH:	8.0 mm
MOUNTING DIMENSIONS:	10.0 mm

DIMENSIONS:

