

[Home](#) > [Products](#) >

B5-4

Product Specifications

Illumination Type Incandescent

Illumination Voltage 240V AC

Voltage

Current Draw 42mA

Life Expectancy 2,000 hrs. avg.

Misc. Notes T20 Glass Bulb BA15D Lamp
Base

LT1 Specifications

Specifications	LT1A: Incandescent, Non-Flashing LT1D: Incandescent, Flashing/Non-Flashing LT1H: LED, Non-Flashing LT1K: LED, Flashing/Non-Flashing									
	Nominal Voltage		12V AC/DC ±10%		24V AC/DC ±10%		120V AC ±10%		240V AC ±10%	
	Internal Fuse Rating		3.15A		3.15A		1A		1A	
	Lamp Rating	LED	12V AC/DC		24V AC/DC		120V AC		N/A	
		Incandescent	12V, 6W		30V, 10W		120V, 7W		240V, 10W	
	Current Required per Lamp	LED			Red	Green	Yellow	White	Blue	N/A
				12V DC	54mA	78mA	54mA	54mA	78mA	
				24V DC	54mA	39mA	54mA	54mA	39mA	
				120V AC	30mA	30mA	30mA	30mA	30mA	
		Incandescent	0.4A ±10%		0.3A ±10%		0.06A ±10%		0.05A ±10%	
		External Contact Capacity		5A		5A		2A		1A
	In-Rush Current per Lamp	LED	Not applicable							
		Incandescent	Below 4.0A		Below 3.0A		Below 0.6A		Below 0.5A	
	Lamp Style	LED	BA15D lamp base							
		Incandescent	T20 glass bulb, BA15D lamp base							
	Lamp Life-Span	LED	100,000 hours (minimum)							
		Incandescent	2,000 hours (average)							
	Lens Colors		Red, Yellow, Green, Blue, White							
	Lens Diameter		2.20" (56mm)							
	Maximum Tiers		5							
	Degree of Protection		IP20 (for indoor use only), NEMA1							
	Flash Rate		LED: 45/minute ±10% (LT1K only) Incandescent: 80/minute ±10% (LT1D only)							
	Insulation Resistance		More than 3MΩ by a DC 500V megger							
	Voltage Resistance		1,500V AC for 1 minute							
	Operating Range		−30 to +40°C (LT1A), −10 to +40°C (LT1D), 15 to 90% relative humidity							
	Vibration Resistance		2.2G maximum							
	Mounting		Base mount (three stud) Pole mount (horizontal or vertical surface) NPT mount (via adaptor) to 1/2"" or 3/4"" NPT conduit Install in an upright position							
	Optional Pole Height		10.75" (273mm)							
Approvals		 File #E70646								
Wire Size		Non-flashing (steady): 20 AWG Flashing: 18 AWG and 20 AWG								

LT1 Accessories

Part Numbers: Accessories

Description	Part No.	Remarks
LED Lamp 	LTXD-1 ②	12V AC/DC See chart for available colors
	LTXD-2 ②	24V AC/DC See chart for available colors
	LTXD-120 ②	120V AC See chart for available colors
Incandescent Lamp 	B5-21	12V AC/DC, 6W
	B5-31	30V, 10W (for use with 24V AC/DC)
	B5-1	120V AC, 7W
	B5-4	240V AC, 10W
Lens 	LT1X-08 ②	See chart for available colors
Top Cap 	LT1X-06	Clear polycarbonate
Mounting Pole 	LT1Z-10	Chrome-plated steel supplied with "L" bracket and two M22 x 1.5 hexagonal nuts
Pole Mounting Fixture 	LT1Z-11	Aluminum fixture for mounting pole-mounted units to horizontal surface; not included with assembled Signalight units
NPT Pole Adaptors 	LT1Z-NPT50	1/2" NPT pole adapter; not included with assembled Signalight units
	LT1Z-NPT75	3/4" NPT pole adapter; not included with assembled Signalight units

② Lens/LED Color Code

Color	Code
Green	G
Red	R
Blue	S
White	W
Yellow	Y



In place of ② specify lens/LED color code from chart at right.