


LOC		DIST				REVISIONS					
G		14		P	F	ZONE	LTR	DESCRIPTION		DATE	APPD
							B	REV & REDRAWN PER 0720-0040-93		4-7-93	1AP DAP

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
6 AWG SOLID OR STRANDED	6 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
6 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 6W* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		DR 4-7-93 TA BRINKMAN		321576		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE		MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 4-7-93 DA PATTERSON		PART NO		
FOR APPLICATION TOOLING INFORMATION			WIRE CROSS SECTIONAL AREA RANGE: 10.5-16.8MM² [20,800-33,100] CIR MILS SOLID OR STRANDED		FINISH TIN PLATE 0.00254[0.00100] MIN THK PER MIL-T-10727		APPD 4-7-93 DE MILLER		NAME		
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				APPD 4-7-93 JL MECKLEY		TERMINAL, RING TONGUE, FLAG, SOLISTRAND™x		
							PRODUCT SPEC -		SIZE		
							APPLICATION SPEC -		CAGE CODE		
							WEIGHT -		DRAWING NO		
									00779		
									C=321576		
									SCALE 8:1		
									SHEET 1 OF 1		