


CHAIN TERMINAL

SRB series (With insulation grip) <Made in Belgium>

LRB is Loose version of S (Strip) RB



DIN 46225 (except *-marked items)

Model No.	Standard	Applicable wire			Material	Finish	Dimensions mm(in.)					Q'ty / reel
		mm²	AWG #	Insulation O.D. mm(in.)			W	L	E	d (dia.)	Material thickness	
SRB-1.0-M3		0.5 to 1.0	20 to 18	2.0 to 3.3 (.079 to .130)	Brass	—	8.0(.315)	21.0(.827)	17.0(.669)	3.2(.126)	0.6(.024)	5,000
SRB-1.0T-M3						Tin-plated						4,000
SRB-1.0-M3-W9.5 *						—						
SRB-1.0T-M3-W9.5 *						Tin-plated						
SRB-2.5-M3		1.0 to 2.5	18 to 14	2.7 to 4.3 (.106 to .169)	Brass	—	8.0(.315)	21.0(.827)		4,000		
SRB-2.5T-M3						Tin-plated						
SRB-2.5-M3-W9.5 *						—						
SRB-2.5T-M3-W9.5 *						Tin-plated						
SRB-1.0-M4		0.5 to 1.0	20 to 18	2.0 to 3.3 (.079 to .130)	Brass	—	8.0(.315)	21.0(.827)		4.3(.169)		5,000
SRB-1.0T-M4						Tin-plated						4,000
SRB-1.0-M4-W9.5 *						—						
SRB-1.0T-M4-W9.5 *						Tin-plated						
SRB-2.5-M4		1.0 to 2.5	18 to 14	2.7 to 4.3 (.106 to .169)	Brass	—	8.0(.315)	21.0(.827)	4,000			
SRB-2.5T-M4						Tin-plated						
SRB-2.5-M4-W9.5 *						—						
SRB-2.5T-M4-W9.5 *						Tin-plated						
SRB-1.0-M5-W8 *		0.5 to 1.0	20 to 18	2.0 to 3.3 (.079 to .130)	Brass	—	8.0(.315)	21.0(.827)	5.3(.209)	5,000		
SRB-1.0T-M5-W8 *						Tin-plated				4,000		
SRB-1.0-M5						—						
SRB-1.0T-M5						Tin-plated						
SRB-2.5-M5-W8 *		1.0 to 2.5	18 to 14	2.7 to 4.3 (.106 to .169)	Brass	—	8.0(.315)	21.0(.827)		4,000		
SRB-2.5T-M5-W8 *						Tin-plated						
SRB-2.5-M5						—						
SRB-2.5T-M5						Tin-plated						
SRB-1.0-M6 *		0.5 to 1.0	20 to 18	2.0 to 3.3 (.079 to .130)	Brass	—	9.5(.374)	21.75(.856)	6.5(.256)	4,000		
SRB-1.0T-M6 *						Tin-plated						
SRB-2.5-M6 *	1.0 to 2.5	18 to 14	2.7 to 4.3 (.106 to .169)	Brass	—							
SRB-2.5T-M6 *					Tin-plated							

Applicator for the semi-automatic press AP-K2N

Contact	Crimp applicator MK-L	
	with safety cover	without safety cover
SRB-1.0(T)-M3/4	APLMK SRB10-W8	APLNC SRB10-W8
SRB-1.0(T)-M5-W8	APLMK SRB10-W8	APLNC SRB10-W8
SRB-1.0(T)-M3/4-W9.5	APLMK SRB10-W9.5	APLNC SRB10-W9.5
SRB-1.0(T)-M5/6	APLMK SRB10-W9.5	APLNC SRB10-W9.5
SRB-2.5(T)-M3/4	APLMK SRB25-W8	APLNC SRB25-W8
SRB-2.5(T)-M5-W8	APLMK SRB25-W8	APLNC SRB25-W8
SRB-2.5(T)-M3/4-W9.5	APLMK SRB25-W9.5	APLNC SRB25-W9.5
SRB-2.5(T)-M5/6	APLMK SRB25-W9.5	APLNC SRB25-W9.5