

# High Precision Tweezers

Handcrafted to perfect tip symmetry and balance, polished edges, superior no-scratch/antiglare satin finish. The right tweezers and material for a successful application. All High Precision Tweezers are available with special coatings: DC, EP, NE, TE. Please refer to technical datasheet on page 44 for more information. Chemical data-charts are available on [www.ideal-tek.com](http://www.ideal-tek.com)



0.SA  
0.S  
0.TA

4 3/4" 120mm  
flat edges, fine tips



00.SA  
00.S  
00.TA

4 3/4" 120mm  
strong, flat edges, thick



000.SA  
000.S

4 3/4" 120mm  
strong, flat radiused edges, fine



0A.SA

4 3/4" 120mm  
same as 0, radiused edges, fine



00B.SA

4 3/4" 120mm  
same 00 with serrated grips



0C9.SA  
0C9.S  
0C9.TA

3 1/2" 90mm  
short, flat edges, fine



0C11.SA  
0C11.S

4 1/4" 110mm  
short, flat edges, fine



00D.SA  
00D.S  
00D.TA

4 3/4" 120mm  
same as 00, serrated tips and grips



1.SA  
1.S  
1.NC  
1.TA

4 3/4" 120mm  
strong, straight, fine



2.SA  
2.S  
2.NC  
2.TA  
2.BR

4 3/4" 120mm  
flat, sharp fine tips



2A.SA  
2A.S  
2A.NC  
2A.TA

4 3/4" 120mm  
flat accurate round tips



2AB.SA  
2AB.S  
2AB.TA

4 3/4" 120mm  
as 2A, curved



2AZ.SA

4 3/4" 120mm  
as 2A, double bent tips



3.SA  
3.S  
3.NC  
3.TA

4 3/4" 120mm  
very sharp, fine




3C.SA  
3C.S  
3C.NC  
3C.TA

4 1/4" 110mm  
as 3, short



3CB.SA  
3CB.S

4 1/4" 110mm  
as 3C, bent tips



3CI.SA  
3CI.TA

4 1/4" 110mm  
as 3C, crush proof, smooth



3F.SA  
3F.S

4 3/4" 120mm  
3mm flat touch, for holding tiny wires



4.SA  
4.S  
4.NC  
4.TA

4 1/4" 110mm  
extra fine tips



4A.SA  
4A.S

4 1/4" 110mm  
as 4, strohger



5.SA  
5.S  
5.NC  
5.TA

4 1/4" 110mm  
extra fine tips, superior finish



5A.SA  
5A.S  
5A.NC  
5A.TA

4 1/2" 115mm  
extra fine tips, superior finish



5B.SA  
5B.S

4 1/4" 110mm  
as 5, bent tips for max visibility



5C.SA  
5C.S  
5C.NC  
5C.TA

4 1/2" 115mm  
as A, extra fine, double bent tips



5TTH.SA  
5TTH.S

4 1/4" 110mm  
anti capillary, extra fine, with lock-ring  
for handling electronic microscope grids



6.SA  
6.S  
6.NC  
6.TA

4 1/2" 115mm  
flat angled, fine



7.SA  
7.S  
7.NC  
7.TA

4 1/2" 115mm  
very fine, curved




7A.SA  
7A.S  
7A.NC

4 1/2" 115mm  
as 7, strong



7B.SA  
7B.S  
7B.TA

4 1/2" 115mm  
as 7, serrated tips



7E.SA  
7E.S

4 1/2" 115mm  
as 7, flat edges



K5HP.SA

high precision tweezers set 00, 2A, 3C, 5, 7  
top quality hard/foam wallet



8.SA  
8.S  
8.TA

length 4 3/4" 120mm, width 0.4" 10mm  
strong flat for straightening wires



10G.SA

4 1/4" 110mm  
fine, serrated tips and grips



11.SA  
11.N

4 3/4" 120mm  
straight, fine tips



12.SA  
12.N

4 3/4" 120mm  
strong, fine tips



14.A.C

11.5 mm



4 1/2" 115mm  
cutting tweezers fine, 90° angled blades



14.AG.W.C

6mm



4 1/2" 115mm  
cutting tweezers for max visibility fine, 90° angled blades



14.AN.C

11mm




4 1/2" 115mm  
same as 14A, rounded tips



15.A.C

12mm



4 1/2" 115mm  
cutting tweezers for soft copper, gold, silver, magnetic wires



15.A.F.W.C

8mm




4 1/2" 115mm  
cutting tweezers for soft copper, gold, silver, magnetic wires



15.A.G.W.C

10mm




4 1/2" 115mm  
cutting tweezers for soft copper, gold, silver, magnetic wires



15.A.N.W.C

8mm




4 1/2" 115mm  
rounded edges cutting tweezers for soft copper, gold, silver, magnetic wires



15.A.P.C

12mm



4 1/2" 115mm  
parallel cutting tweezers for soft copper, gold, silver, magnetic wires



15.A.S.W.C

10mm



4 1/2" 115mm  
rounded edges cutting tweezers for soft copper, gold, silver, magnetic wires




27.SA  
27.S

5 1/3" 135mm  
strong, sharp, fine tips



51S.SA  
51S.S  
51S.TA

4 1/2" 115mm  
as 5A, bent tips for max visibility



52A.SA  
52A.S  
52A.TA

4 3/4" 120mm  
as 2A, crush proof, smooth action



152.S

3 3/4" 98mm  
precision miniature cutting tweezers



775.SA

6 1/8" 155mm  
Fine, bent tips epoxy coated handles



A.SA  
A.S

4 3/4" 120mm  
strong, precision tips



AC.SA  
AC.S

4 1/4" 110mm  
strong tips, serrated grips



AM.BR

4 3/4" 120mm  
precision brass tweezers anti-sparking



D.SA

4 1/4" 110mm  
precision strong, flat tips



F.SA  
F.S  
F.NC

4 3/4" 120mm  
as 2A, flat and squared tips



H.SA  
H.S

3 1/2" 90mm  
dove tailed fine tips



P.SA  
P.S  
P.NC  
P.TA

4 3/4" 120mm  
fine, strong tips



S.SA  
S.S

4 3/4" 120mm  
very fine tips