


Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	8 STR/FLEX
Wire Type	Stranded Copper: Class B & C Compact, Class G, H, I, K, M, Locomotive
Wire Strip Length	3/4 in.
Stud Size	1/4 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	RED
Panduit Die Index No. on Barrel	P21
Alternate Industry Die Index No. () on Barrel	N/A



Technical drawing of a Panduit wire management component. The drawing shows a rectangular part with a circular hole. Dimensions are given: .48±.04 for the total height, .25±.04 for the distance from the bottom edge to the center of the hole, and .27±.02 DIA for the hole diameter. The part is labeled 'PANDUIT' and '8 STR/FLEX LCBX8-14F'. A 'Wire inspection window' is indicated on the right side.



SCALE N/A	DRAWING NO / CAD FILE LCBX8-14F-CUST
--------------	---