






General ordering data

Order No.	4061180000
Part designation	SSS Relais 24V/24V 0,1Adc
Version	Solid-state relay, 3...48 Vdc , 100 mA/ DC , Plug-in connection
EAN	4032248415076
Qty.	1 pc(s).

Approvals

Approvals institutes



Control side

Rated control voltage	16 V DC.....30 V DC
-----------------------	---------------------

General data

Ambient temperature (operational)	-20 °C...+60 °C
Storage temperature	-40 °C...+70 °C
Climate	40°C/93% rel. humidity, no condensation
Weight	3.65 g
Connection system	Plug-in connection

Insulation coordination (EN 50 178)

Dielectric strength for control side - load side	2.5 kV
--	--------

Load side

Nominal switching current	100 mA/ DC
Nominal switching voltage	3...48 Vdc
Status indicator	No

Classifications

ETIM 2.0	EC001504
ETIM 3.0	EC001504
eClass 4.1	27-27-09-00
eClass 5.0	27-27-09-90
eClass 5.1	27-27-09-90

Similar products

Order No.	Part designation	Version
8633020000	MOS 5Vdc / 24Vdc 0,1A	Optocoupler, 3... 48 V DC , 0.1 A , Screw connection
8633010000	MOZ 5Vdc / 24Vdc 0.1A	Optocoupler, 3... 48 V DC , 0.1 A , Tension clamp connection
8607340000	MOS 24Vdc / 24Vdc 0.1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Screw connection
8607360000	MOZ 24Vdc / 24Vdc 0,1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Tension clamp connection
8607690000	MOS 120Vuc / 24Vdc 0.1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Screw connection
8607730000	MOZ 120Vuc / 24Vdc 0.1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Tension clamp connection
8607710000	MOS 230Vac / 24Vdc 0.1A	Optocoupler, 3 V...48 V DC , 0.1 A , Screw connection
8607750000	MOZ 230Vac / 24Vdc 0.1A	Optocoupler, 3 V...48 V DC , 0.1 A , Tension clamp connection
4061230000	SSS Relais 60V/24V 0,1Adc	Solid-state relay, 3...48 Vdc , 100 mA/ DC , Plug-in connection