









Amp	Volt	Hz	IP Ident. colour + h	Part No.	Plugs	2 P +  IEC/EN 60 309	 g	EAN-No. 4015609...																												
					flexible cable entry	   <table><tr><th>Ampère</th><th>d</th><th>Øe</th><th>f</th><th>m</th><th>n</th><th>Øp</th></tr><tr><td>16 A</td><td>143</td><td>51</td><td>60</td><td>108</td><td>37</td><td>7/13</td></tr><tr><td>32 A</td><td>181</td><td>72</td><td>79</td><td>138</td><td>46</td><td>11/24</td></tr><tr><td>63 A</td><td>252</td><td>81</td><td>97</td><td>192</td><td>67</td><td>15/33</td></tr></table>	Ampère	d	Øe	f	m	n	Øp	16 A	143	51	60	108	37	7/13	32 A	181	72	79	138	46	11/24	63 A	252	81	97	192	67	15/33	10 111 10 202 5 475	011919 011896 011940 013364 013357 013395 014552 014545 014569
Ampère	d	Øe	f	m	n	Øp																														
16 A	143	51	60	108	37	7/13																														
32 A	181	72	79	138	46	11/24																														
63 A	252	81	97	192	67	15/33																														
					inverted cable entry	   <table><tr><th>Ampère</th><th>d</th><th>Øe</th><th>f</th><th>m</th><th>n</th><th>Øp</th></tr><tr><td>16 A</td><td>111</td><td>51</td><td>60</td><td>108</td><td>37</td><td>8/15</td></tr></table>	Ampère	d	Øe	f	m	n	Øp	16 A	111	51	60	108	37	8/15	10 101	122417 122400 173686														
Ampère	d	Øe	f	m	n	Øp																														
16 A	111	51	60	108	37	8/15																														
					gland entry	   <table><tr><th>Ampère</th><th>d</th><th>Øe</th><th>f</th><th>m</th><th>n</th><th>Pg</th></tr><tr><td>16 A</td><td>123</td><td>51</td><td>60</td><td>118</td><td>37</td><td>13,5</td></tr><tr><td>32 A</td><td>155</td><td>73</td><td>79</td><td>133</td><td>46</td><td>21</td></tr><tr><td>63 A</td><td>240</td><td>81</td><td>97</td><td>192</td><td>67</td><td>36</td></tr></table>	Ampère	d	Øe	f	m	n	Pg	16 A	123	51	60	118	37	13,5	32 A	155	73	79	133	46	21	63 A	240	81	97	192	67	36	10 112 10 211 5 475	012350 012336 012381 013753 013746 013760 014774 014767 014781
Ampère	d	Øe	f	m	n	Pg																														
16 A	123	51	60	118	37	13,5																														
32 A	155	73	79	133	46	21																														
63 A	240	81	97	192	67	36																														
					flexible cable entry, with lockable facility when used with panel socket 512 306, 512 304 und 512 309	   <table><tr><th>Ampère</th><th>d</th><th>e</th><th>f</th><th>m</th><th>n</th><th>Øp</th><th>u</th></tr><tr><td>16 A</td><td>143</td><td>51</td><td>60</td><td>108</td><td>37</td><td>7/13</td><td>61</td></tr></table>	Ampère	d	e	f	m	n	Øp	u	16 A	143	51	60	108	37	7/13	61	10 113	012688 128815 128822												
Ampère	d	e	f	m	n	Øp	u																													
16 A	143	51	60	108	37	7/13	61																													