

CATALOG LISTING

BZE6-2RQ9-S

PAGE 1 OF 1

REPLACES

PR-14687

CHECK

29AUG07

PSR

10NOV05

RJ


CHECK


20MAR96

S A V

RASTER

DRAWN



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION 
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — — — 9-13 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE — — — — — 4 OZ MIN		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
DIFFERENTIAL TRAVEL — — — — .002 MAX	L74 15A 125, <u>250</u> OR 480 VAC 2A 600 VAC 1/8HP 125 VAC, 1/4HP <u>250</u> VAC 1/2A 125 VDC, 1/4A 250 VDC   1.5A, 240 Vac	ONE PLACE (.0) ±.030
OVERTRAVEL — — — — — .140 MIN		TWO PLACE (.00) ±.015
SWITCH - BASIC REPLACEMENT --- BZ-2RQ69		THREE PLACE (.000) ±.005
		ANGLES ±
		WEIGHT .56 LB

- NOTES
- 1 - ZINC ENCLOSURE FINISHED WITH GRAY PAINT
 - 2 - 3X 6-32 UNC X (.219) BINDING HEAD TERMINAL SCREW AND CUPWASHER
 - 3 - FURNISHED UNASSEMBLED
 - 4 - SEAL RATING: NEMA 1 IP40