





PRODUCT NO. ④	DIM. A	DIM. B	DIM. C	STYLE	POSITIONS LOADED	CONTACT PLATING ①	NOTES
69255-X01YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X02YLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	5u" Au + high performance lubricant	-
-X03YLF	-	-	15.62/0.615	UNKEYED	2,3,4,5,6,7	5u" Au + high performance lubricant	-
-X04YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X05YLF	-	-	15.62/0.615	UNKEYED	ALL	1.27um /50u" GXT	-
-X06YLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	1.27um /50u" GXT	-
-X07YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 5
-X08YLF	-	-	15.62/0.615	UNKEYED	3,4,5,6	5u" Au + high performance lubricant	-
-X09YLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6
-X10YLF	-	-	13.62/0.536	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6




SECTION B-B

KEYED STYLE
SPECIAL BEND REQUIRED BY CUSTOMER FOR P/N 69255-001BLE



DETAIL C
(OPTIONAL DESIGN)



BOARD LAYOUT
VIEWED FROM TOP

NOTES :

① SPECIAL PACKAGING.

② SOLDER TAIL LENGTH :

- X = 0 [3.18 ±0.51 /0 .125 ±0.020]
- X = 1 [8.13 ±0.51 /0 .320 ±0.020]
- X = 2 [5.30 ±0.51 /0 .208 ±0.020]
- X = 3 [3.70 ±0.51 /0 .145 ±0.020]
- X = 4 [4.50 ±0.51 /0 .177 ±0.020]

[FOR X = 1 TO 4 , IF WIRE TRUE POSITION IS NOT APPLICABLE.]
PACKAGING SPEC. IS GS-14-428

③ COLOR OF HOUSING :

- Y = NIL (BLACK HOUSING)
- Y = W (WHITE, RA1013 HOUSING)
- Y = G (GRAY, HOUSING)

④ SPECIAL REQUIREMENT :

SEE DETAIL C FOR P/N 69255-001B
FOR FEATURE DETAILS.

⑤ NO PANEL STOPS ON -X09Y AND -X10Y.

⑥ THIS PIN NUMBERING OPPOSITE TO

FCC, PART 68, SUB-PART F REQUIREMENTS

⑦ PART NUMBERS WITH LF IN THE END ARE LEAD FREE.

⑧ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AN OTHER COUNTRY
REGULATION AS DESCRIBED IN GS-22-008.

⑨ THE HOUSING TEMPERATURE WITHSTAND EXPOSURE TO 260C PEAK
TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A
1.5 MM MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.

⑩ PLATING OPTION:

MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code	surface	tolerance	projection	product family
ISDI302	ISDI101	ISDI406	MOD JACK	
ltr ecn nqdr date	tolerances unless otherwise specified			
AJ ELX-N-15334 Henry	07/18/13	angle 8	mm	
-	-	0.X±0.3		
-	-	0.XX±0.15		
-	-	0.XXX±0.05		
AD N08-0239 MHT	11/10/08	0°±2'	scale 2.0	
AE N09-0092 SI MM	01/13/10chr	JANET	2/22/00	
AF ELX-N-0106751 MM	3/14/12 engr	M.CHENG	12/19/00	
AG ELX-N-13788 Henry	01/02/13chr	M.CHENG	12/19/00	
AH ELX-N-1406 Henry	02/18/13appd	M.CHENG	12/19/00	
sheet index	revision			
	sheet			

8 POS VERTICAL
PC.B. MOD JACK ASSY

awg no sheet 2 of 3 size A4
type Product Customer Drawing 69255



Copyright FCI.

1 | 2

FCIconnect.com

3 |

4

PRODUCT NO. ④	DIM. A	DIM. B	DIM. C	STYLE	POSITIONS LOADED	CONTACT PLATING ①	NOTES
69255-X01YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X02YHLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	5u" Au + high performance lubricant	-
-X03YHLF	-	-	15.62/0.615	UNKEYED	2,3,4,5,6,7	5u" Au + high performance lubricant	-
-X04YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	-
-X05YHLF	-	-	15.62/0.615	UNKEYED	ALL	1.27um /50u" GXT	-
-X06YHLF	1.25 /0.050	2.69 /0.106	15.62/0.615	KEYED	ALL	1.27um /50u" GXT	-
-X07YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 1
-X08YHLF	-	-	15.62/0.615	UNKEYED	3,4,5,6	5u" Au + high performance lubricant	-
-X09YHLF	-	-	15.62/0.615	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6
-X10YHLF	-	-	13.62/0.536	UNKEYED	ALL	5u" Au + high performance lubricant	NOTE 6

MEETS PIP PROCESS PRODUCT NO.

A

A

3

B