



(1,27 mm) .050"

FW-10-04-L-D-440-150

FW-40-02-F-D-425-075

FW-20-02-F-D-200-140

FW-TH SERIES

THROUGH-HOLE MICRO BOARD STACKER

SPECIFICATIONS

For complete specifications see www.samtec.com?FW-TH

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Plating:
Sn or Au over
50µ" (1,27 µm) Ni
Operating Temp Range:
-55°C to +125°C
RoHS Compliant:
Yes

Processing:
Lead-Free Solderable:
Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Mates with:
CLP, FFSD, FLE


Low profile or
skyscraper styles

(1,27 mm)
.050" pitch

Variable
board spacing

ALSO AVAILABLE (MOQ Required)

- Smaller stack heights
Contact Samtec.



Note: For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Note: This Series is non-standard, non-returnable.