

POS. 1	POS. 2	POS. 3
		
ON	OFF	MOM
2-3	OPEN	2-1
 Comm.		 Comm.

- Rating: 2 A/250 VAC
5/120 VAC or 28VDC
- Contact Resistance: 10mΩmax. initial
@ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩmin.
- Dielectric Strength: 1,000 V RMS@ sea level

- Mechanical Life: 30,000 make-and-break cycles.
- Operating Temperature: -30°C to 85°C

- RoHS compliant by exemption

- Case & Bushing: glass filled nylon 6/6, flame retardant, heat stabilized
- Actuator: nylon, black std. Internal O-ring seal standard with all actuators.
- Frame: spring steel, black std.
- Switch Support: brass or steel, tin plated
- Terminals / Contact: silver or gold plated copper alloy
- Actuator Pivot & Mounting Bracket: nylon
- Actuator Pivot Retainer: stainless steel

Mountain Switch

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7019-EVX](#)