

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192130011

Status:

Active

Overview:

Wire Pins

Description:

Avikrimp™ Wire Pin Terminal for 16-14 AWG Wire




image - Reference only

Series

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	19213
Comments	Pin Length 9.40mm (.370"). Packaged Loose Piece in Bag
Overview	Wire Pins
Product Name	Wire Pin
Physical	
Flammability	94V-0
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min: Mating (µin)	39
Plating min: Mating (µm)	1.00
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.32mm (.170") max.
Wire Size AWG	14, 16
Wire Size mm²	N/A
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	WP-8614
Reference - Drawing Numbers	
Sales Drawing	CD81200

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Halogen-Free Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19213Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640051400
Hand Crimp Tool	0640011400

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION