

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130153-0029

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Super-Safeway® In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, Molded NEMA 5-15 Tri-Tap, 15A, 120V, 0.61m (2.0') Cord Length

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Product Literature (PDF)

Product Literature (PDF)

|                               |                                                  |
|-------------------------------|--------------------------------------------------|
| Agency Certification          |                                                  |
| UL                            | E66308                                           |
| General                       |                                                  |
| Product Family                | Power Distribution                               |
| Series                        | 130153                                           |
| Enclosure Rating              | NEMA 3R                                          |
| GFCI Reset                    | Automatic                                        |
| Mounting Style                | Portable                                         |
| Open Neutral Relay            | Yes                                              |
| Overview                      | Ground Fault Circuit Interrupter (GFCI) Products |
| Product Literature Order No   | 987650-7737, 987651-0452                         |
| Product Name                  | Super-Safeway™                                   |
| Receptacle Type               | N/A                                              |
| Type                          | GFCI Industrial Duty, Single Phase               |
| UPC                           | 78678888260                                      |
| Woodhead                      | Yes                                              |
| Physical                      |                                                  |
| Cord Diameter                 | 10.92mm (.430")                                  |
| Cord Grip Body Size           | Internal Double C-Clamp                          |
| Cord Length                   | 0.61m (2.0')                                     |
| Feed-Thru                     | Yes                                              |
| Flip Lid                      | No                                               |
| Material - Housing            | Nylon                                            |
| Number of Receptacles         | 3                                                |
| Packaging Type                | Bag                                              |
| Electrical                    |                                                  |
| Cord Type                     | 12/3 SJTW                                        |
| Current - Maximum per Contact | 15A                                              |
| GFCI                          | Yes-In-line                                      |
| Ground Continuity Monitor     | No                                               |
| NEMA Configuration            | NEMA 5-15                                        |
| Voltage - Maximum             | 120V                                             |
| Material Info                 |                                                  |
| Old Part Number               | 15050-3TTA                                       |



EU RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130153Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION