






**FEMALE PLUG WITH STRAIGHT  
SOLDER PIN PIN SPACING 5 MM / 0.  
197 IN 100% PROTECTED AGAINST  
MISMATING**  
722-132 TO 722-150

|                                                      |                                           |
|------------------------------------------------------|-------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 722-134                                   |
| Measured voltage (Measured voltage / V)              | 320                                       |
| Measured shock voltage (Measured shock voltage / kV) | 4                                         |
| Pollution degree (Pollution degree)                  | 2                                         |
| Current intensity (Current intensity / A)            | 12                                        |
| RM (PIN SPACING / mm)                                | 5                                         |
| P (NO. OF POLES)                                     | 4                                         |
| Height (Height / mm)                                 | 18.25                                     |
| Width (Width / mm)                                   | 21.5                                      |
| Depth (Depth / mm)                                   | 11.6                                      |
| COLOR (COLOR)                                        | lichtgrau                                 |
| Comment (Comment)                                    | L = (No. of poles x Pin Spacing) + 1,5 mm |
| Dimensions (Dimensions)                              | 1.3 +0.1 mm                               |