

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1201000002

Status: **Active**

Overview: PROFIBUS Solutions

Description: Micro-Change (M12) Field Attachable Connector, PROFIBUS Shielded, Straight Male

Documents:

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	<u>120100</u>
IP Rating	IP67
Material - Contact	Brass
Overview	PROFIBUS Solutions
Product Name	Micro-Change (M12), PROFIBUS
Type	Field Attachable Connector
UPC	78678850052

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Reverse
Material - Connector Body	N/A
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver
Net Weight	48.534/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	22

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number BA5S06-32

Reference - Drawing Numbers

Sales Drawing	1201000002-000, SD-120100-002
---------------	-------------------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION