



Dimensions: mm

Specifications :

- Sync input impedance: 1M Ω
- Pulse repetition rate: 0.5 pps/ 400 pps
- Pulse width in pulser output at 100 mA load: 1 μ sec
- Output current:
 - Pulser mode: 100 mA sink/source
 - Square wave output: 5 mA sink/source
- Power supply protection: ± 25 V/25 sec
- Output protection: ± 35 V/15 sec
- Maximum allowable supply voltage: ± 20 V
- Operating supply voltage range: 5 V to 15 V
- Maximum output allowable connecting voltage: ± 35 V
- Free air operating temperature range: 0°C to 50°C
- Maximum sync input voltage: ± 120 V/15 sec

383-LP541

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PSP:

[383-LP541](#)