


# TUNING FORK CRYSTAL UNIT (SMD • Ceramic Package)

RoHS compliant / Pb free

## CM315


3000pcs/reel




### FEATURES

- Tuning fork crystal with ceramic packaged type.
- High-density SMD type  
Ultra-light weight with ultra-miniature packaging.  
High-stability assured with tight vacuum sealing.
- Most appropriate for portable devices and mobile telecommunications devices.

### DIMENSION [mm]



### SOLDER PAD LAYOUT [mm]



### STANDARD SPECIFICATIONS

Item	Model	CM315	Conditions
Nominal Frequency	$f_0$	32.768kHz	
Frequency Tolerance	$\Delta f/f_0$	$\pm 20\text{ppm}$	at 25°C
Load capacitance	$C_L$	9.0pF, 12.5pF	Need to specify your requirement
Operating Temperature Range	$T_{OPR}$	-40°C ~ +85°C	
Storage Temperature Range	$T_{STR}$	-55°C ~ +125°C	
Turnover Temperature	$T_M$	25°C $\pm 5^\circ\text{C}$	
Temperature Coefficient	$\beta$	$-0.034 \pm 0.006\text{ppm}/^\circ\text{C}^2$	
Motional (series) resistance	$R_1$	70K $\Omega$ Max.	at 25°C
Level of drive	$D_L$	1 $\mu\text{W}$ Max.	
Aging (first year)	$\Delta f/f_0$	$\pm 3\text{ppm}$ Max.	25°C $\pm 3^\circ\text{C}$
Shunt capacitance	$C_0$	0.95pF Typ.	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Citizen:

[CM315-32.768KDZC-UT](#) [CM315-32.768KDZY-UT](#) [CM315-32.768KDZF-UT](#) [CM315-32.768KAZB](#) [CM315D-32.768KEZF-UT](#)