




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN 4260: CN RELEASE	9/15/09	D. CASTRO
D	ECN 6458: USE NEW LOGO, REVISE DIMS .33 TO .43, .670 TO .675	10/12/12	D.FRISIELLO
E	ECN 6692: ADDED BOTTOM VIEW FOR CLARITY, ADDED ROHS	2/20/13	D.FRISIELLO



NOTES:

MATERIAL:

COUPLER HOUSING: ABS, UL94V-0.
CONNECTOR PLASTIC: PBT WITH GLASS FIBER
CONNECTOR CONTACTS: BRASS
CONNECTOR SHELL: BRASS
PCB: EPOXY GLASS FP-4, 94V-0 FLAMMABILITY RATING

FINISH:

COUPLER HOUSING: CHROME
CONNECTOR CONTACTS: GOLD, 30μ MICRO INCH
CONNECTOR SHELL: NICKEL



ENVIRONMENTAL:

OPERATING TEMPERATURE: -20°C TO +80°C


PACKAGING:

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

WIRING MAP



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY E. STAUBLE	2008.05.12		
	CHECKED BY D. CASTRO	2008.05.13		
	APPROVED BY D. PARHAM	2008.05.14		
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY USB	
			PRODUCT DESCRIPTION USB A-A PANEL ADPT SHIELDED	
			SIZE A	FSCM NO. 43321
			DWG. NO. ECF504-UAAS	REV. E
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: ECF504-UAAS.SLDDRW	SHEET 1 OF 1