

Cable sleeve - CES-STPG-GY-2X3 - 1410424

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Small, slotted cable sleeves suitable for two cables with a diameter of 2 ... 3 mm, material: SEBS

Product Description

drilled special sleeve in IP44



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Custom tariff number	85472000
Country of origin	Germany

Technical data

Dimensions

External cable diameter	2x 2 mm ... 3 mm
Length	29.5 mm
Width	19.5 mm
Height	17 mm

Ambient conditions

Degree of protection	IP44
Ambient temperature (operation)	-40 °C ... 80 °C (static)

General

Product description	drilled special sleeve in IP44
No. of conductors	2
Material	SEBS
Flammability rating according to UL 94	V0
Color	gray

Cable sleeve - CES-STPG-GY-2X3 - 1410424

Technical data

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27081002
eCl@ss 4.1	27081002
eCl@ss 5.0	27081002
eCl@ss 5.1	27081002
eCl@ss 6.0	27081002
eCl@ss 7.0	27081002
eCl@ss 8.0	27069216

ETIM

ETIM 3.0	EC000879
ETIM 4.0	EC002498
ETIM 5.0	EC000451

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approvals submitted

Cable sleeve - CES-STPG-GY-2X3 - 1410424

Approvals

Approval details


UL Recognized 

cUL Recognized 

cULus Recognized 

Drawings

Dimensional drawing



Dimensional drawing