



English | 简体中文 | 日本語

Search by Part Number

GO

Search Site by keyword

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > Clock / Timing Devices > PC-Notebook-Server Clocks > Clock Synthesizer by Chipset Vendor > Desktop Chipsets > 9LPR462 > 9LPR462AGLFT

You may also like...

9LPR462AGLFT

Category: Desktop Chipsets

Generic Part: 9LPR462

Market Group: PC CLOCK

Description: PC MAIN CLOCK
Output Features: 2 - pairs of CPU pairs, AMD K8 Greyhunt compatible 8 - pairs of SRC pairs 4 - pairs of ATIG pairs 1 - HyperTransport 66MHz clock seed 2 - 48MHz USB clock 3 - 14.318MHz Reference clock

Save both

Parameters

Temperature	C
Voltage	3.3 V
Package	TSSOP 64
Speed	NA
Status	Active
Sample	Yes
Minimum Order Quantity	1000
Factory Order Increment	1000

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Package	TSSOP 64 (PAG64)
Description	TSSOP 6.1 MM 0.5MM PITCH
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	G
Package Type	TSSOP
Lead Count	64
Length	17.0 mm
Width	6.1 mm
Thickness	1.0 mm
Pitch	0.5 mm
Tube / Tray	TUBE
Quantity per Tube/Tray	28
Quantity per Reel	1000
Moisture Sensitivity Level (MSL)	1
Moisture Exposure Floor Life	Unlimited@<30C/85%RH
Peak Reflow Temperature	260°C
Rebake Conditions	NA
Related Package Documents	view documents

Home | Site Map | Legal | Careers | Contact Us | Quality | RSS What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. All Rights Reserved.