


## Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 1A/125VAC
- Electrical life: 10,000 operations
- Insulation resistance: 1000MΩ (min.) @ 500VDC
- Dielectric Strength: 100VAC for 1 minute
- Contact resistance: 20mΩ (max.)

Mouser Stock No.	Type	Circuit	Button Color
10PA111	SPST	OFF-(ON)	Red
10PA112	SPST	OFF-(ON)	Black
10PA121	SPST	ON-(OFF)	Red
10PA122	SPST	ON-(OFF)	Black

**Mechanical Specifications:**

- Mechanical life expectancy: 30,000 operations

**Soldering Specifications:**

- Temperature: 270°C for 3 sec. (Max.)

**Pushbutton Switches**  
10PA111, 10PA112, 10PA121, 10PA122

**Mountain**  
**Switch**

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[10PA112](#) [10PA111](#) [10PA122](#) [10PA121](#)